



Click [here](#) for the 3D model.

**General Information**

Series	C4G
Dielectric	Metallized Polypropylene
Style	Axial
Features	Switching
RoHS	Yes
Lead	Wire Leads
Typical Component Weight	7.6 g
Miscellaneous	Polyester Tape & Resin Protection.

**Dimensions**

D	17.5mm MAX
L	33mm MAX
LL	40mm +/-5mm
F	1mm NOM

**Packaging Specifications**

Packaging	Bulk, Bag
Packaging Quantity	150

**Specifications**

Capacitance	2.2 uF
Tolerance	5%
Voltage DC	400 VDC
Voltage AC	250 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	45 V/us
ESR	4.4 mOhms (100kHz)
Ripple Current	9 Amps (100kHz 70C), 99 Amps (Peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.