

C921U332MZVDBA7317

Obsolete

C900AC SFTY X1-440 Y2-300, Ceramic, 3,300 pF, 20%, 440 VAC (X1), 300 VAC (Y2), Y5V, 10 mm





The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

Click here for the 3D model.

General Information	
Series	C900AC SFTY X1-440 Y2-300
Style	Radial Disc
RoHS	Yes
Termination	Tin
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
Halogen Free	Yes
Typical Component Weight	600 mg

Dimensions	
D	9mm MAX
T	5mm MAX
S	10mm +/-1mm
H0	18mm +2/-0mm
F	0.55mm +/-0.1mm

Packaging Specifications	
Packaging	Ammo
Packaging Quantity	1000

Specifications	
Capacitance	3,300 pF
Tolerance	20%
Voltage AC	440 VAC (X1), 300 VAC (Y2)
Dielectric Withstanding Voltage	2,600 VDC
Temperature Range	-40/+125°C
Temp. Coefficient	Y5V
Dissipation Factor	5%
Insulation Resistance	10 GOhms
Safety Class	X1/Y2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO