


## CC0805CRNPO9BN8R2

CC NPO, Ceramic,  $8.2\,\mathrm{pF},\,\mathrm{+/-0.25\,pF},\,50\,\mathrm{VDC},\,\mathrm{COG},\,\mathrm{SMD},\,\mathrm{MLCC},\,\mathrm{General}$  Purpose, 0805





General Information	
Series	CC NPO
Style	SMD Chip
Description	SMD, MLCC, General Purpose
RoHS	Yes
Termination	Tin
AEC-Q200	No
Halogen Free	Yes
MSL	1

Click here for the 3D model.

Dimensions	
Chip Size	0805
L	2mm +/-0.1mm
W	1.25mm +/-0.1mm
Т	0.6mm +/-0.1mm
В	0.5mm +/-0.25mm

Packaging Specifications	
Packaging	T&R, 178mm, Paper Tape
Packaging Quantity	4000

Specifications	
Capacitance	8.2 pF
Tolerance	+/-0.25 pF
Voltage DC	50 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Dissipation Factor	0.18%
Insulation Resistance	10 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/20/2025 © 2006 - 2025 YAGEO