


## CC0805KRX7R9BB154

**General Information** 

Series

CC X7R, Ceramic, 0.15 uF, 10%, 50 VDC, X7R, SMD, MLCC, General Purpose, 0805





Style	SMD Chip
Description	SMD, MLCC, General Purpose
RoHS	Yes
Termination	Tin
AEC-Q200	No
Halogen Free	Yes
MSL	1

CC X7R

Click here for the 3D model.

Dimensions	
Chip Size	0805
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
Т	0.85mm +/-0.1mm
В	0.5mm +/-0.500mm

Packaging Specifications	
Packaging	T&R, 178mm, Paper Tape
Packaging Quantity	4000

Specifications		
Capacitance	0.15 uF	
Tolerance	10%	
Voltage DC	50 VDC	
Temperature Range	-55/+125°C	
Temp. Coefficient	X7R	
Dissipation Factor	2.5%	
Insulation Resistance	10 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/20/2025 © 2006 - 2025 YAGEO