



Click [here](#) for the 3D model.

**General Information**

Series	CC Y5V
Style	SMD Chip
RoHS	Yes
Termination	Tin

**Dimensions**

L	2mm +/-0.2mm
W	1.25mm +/-0.20mm
T	1.25mm +/-0.2mm
B	0.5mm +/-0.25mm
Case Code (EIA / mm)	0805 / 2012

**Packaging Specifications**

Packaging	T&R, 178mm, Plastic Tape
Packaging Quantity	3000

**Specifications**

Capacitance	22 uF
Tolerance	-20/+80%
Voltage DC	6.3 VDC
Temperature Range	-30/+85°C
Temp. Coefficient	Y5V
Dissipation Factor	20%
Insulation Resistance	22.7 MOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.