


## CX02M476K

Aliases (T363D476K035AS)

T363, Tantalum, MnO2 Tantalum, Military/High Reliability, 47 uF, 10%, 35 VDC, Radial, Solid Tantalum, Dipped, Military, MIL-PRF-49137/2, CX02 Style



Click [here](#) for the 3D model.

General Information	
Series	T363
Dielectric	MnO2 Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Dipped, Military, MIL-PRF-49137/2, CX02 Style
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a>
SCIP Number	0c1392c3-c7b9-4178-827c-fa26617a3178
Termination	Lead (SnPb)
Lead	Formed
Qualifications	MIL-PRF-49137/2, CX02
Construction	Conformal

Specifications	
Capacitance	47 uF
Tolerance	10%
Voltage DC	35 VDC (85C), 1.75 VDC (85C Reverse)
Temperature Range	-55/+85°C
Dissipation Factor	6%
Leakage Current	10 uA (25°C)

Dimensions	
D	10.16mm MAX
H	19.05mm MAX
S	6.35mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.64mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.