


CX12N475M

Aliases (T369B475M050AS)

T369, Tantalum, MnO2 Tantalum, Military/High Reliability, 4.7 uF, 20%, 50 VDC, Radial, Solid Tantalum, Dipped, Military, MIL-PRF-49137/2, CX12 Style



Click [here](#) for the 3D model.

General Information

Series	T369
Dielectric	MnO2 Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Dipped, Military, MIL-PRF-49137/2, CX12 Style
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	Oc1392c3-c7b9-4178-827c-fa26617a3178
Termination	Lead (SnPb)
Lead	Formed
Qualifications	MIL-PRF-49137/2, CX12
Construction	Conformal

Dimensions

D	6.35mm MAX
W	6.35mm +/-0.64mm
H	12.7mm MAX
S	3.18mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.51mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1000

Specifications

Capacitance	4.7 uF
Tolerance	20%
Voltage DC	50 VDC (85C), 2.5 VDC (85C Reverse)
Temperature Range	-55/+85°C
Dissipation Factor	5%
Leakage Current	1.9 uA (25°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.