


FLLD31K0APV11

Aliases (LLD31K0APV11)

Obsolete

EMI Filters, KEMET, FLLD3-PV, Chassis Mount, Noise Suppression, 350x230x170mm



Click [here](#) for the 3D model.

General Information

Series	FLLD3-PV
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, With Y Capacitor
Features	Three Phase, High Performance, High Voltage
Phase	Three-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL 1283
Lead	Threaded Studs M12
Terminal Type	Threaded Studs M12

Dimensions

L	350mm NOM
W	230mm NOM
H	170mm NOM
L1	145mm NOM
W1	255mm NOM
W2	280mm NOM
U	60mm NOM
X	8mm NOM
Y	40mm NOM
Z	55mm NOM
I	20mm NOM
N	14mm NOM
M (Earth)	Threaded Studs M12
Lead	Threaded Studs M12

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	17,000 g

Specifications

Voltage AC	520 VAC
Rated Frequency	50-60 Hz
Rated Current	1000 A (50°C)
Ripple Current	1000 A (50°C)
Rated Temperature	50°C
Temperature Range	-40/+100°C
Climate Category	40/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Max Power Loss	75 W (25°C 50 Hz)
Leakage Current	5 mA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.