
KHB472KN51DGCZA

Obsolete

KHB DISC Comm Y5P HV, Ceramic, 4,700 pF, 10%, 1,000 VDC, Y5P, 7.5 mm



Click here for the 3D model.

General Information	
Series	KHB DISC Comm Y5P HV
Style	Radial Disc
RoHS	Yes
Termination	Tin
Failure Rate	N/A
Miscellaneous	Climate Category: 55/125/21.

Dimensions	
D	12.5mm MAX
T	4.5mm MAX
S	7.5mm NOM
F	0.6mm +/-0.1mm

Packaging Specifications	
Packaging	T&R, 360mm, H0 = 16mm, Component Pitch = 25.4mm
Packaging Quantity	500

Specifications	
Capacitance	4,700 pF
Tolerance	10%
Voltage DC	1000 VDC
Dielectric Withstanding Voltage	2,000 VDC
Temperature Range	-30/+85°C
Temp. Coefficient	Y5P
Dissipation Factor	2.5%
Insulation Resistance	10 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO