



Click [here](#) for the 3D model.

General Information

Series	RAD LDD Mil PRF123
Style	Radial
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	be36caea-47e6-4511-b5f2-d43a abdeb4b5
Termination	Lead (SnPb)
Lead	Wire Leads
Failure Rate	N/A
Testing and Reliability	MIL-PRF-123
Qualifications	MIL-PRF-123
Notes	Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk.

Dimensions

L	12.19mm +/-0.51mm
H	12.19mm +/-0.51mm
T	3.56mm +/-0.25mm
S	10.16mm +/-0.51mm
LL	31.75mm MIN
F	0.635mm +/-0.051mm

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

Specifications

Capacitance	0.47 uF
Tolerance	10%
Voltage DC	100 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	BX
Dissipation Factor	2.5%
Insulation Resistance	2.1 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.