


[Click here](#) for the 3D model.

General Information

| | |
|----------------|------------------------------------|
| Series | FLLD4-TH |
| Style | Chassis Mount |
| Description | EMI Filter, Chassis Mount, Compact |
| Features | High Performance |
| Phase | Three-phase + Neutral |
| RoHS | Yes |
| Qualifications | IEC/EN 60939 |
| Terminal Type | Terminal Block |

Dimensions

| | |
|-----------|-------------------|
| L | 120mm NOM |
| W | 115mm NOM |
| H | 80mm NOM |
| L1 | 80mm NOM |
| W1 | 127.5mm NOM |
| W2 | 143mm NOM |
| J | 32mm NOM |
| K | 6.5mm NOM |
| M (Earth) | Threaded Studs M6 |

Specifications

| | |
|--------------------------|------------------|
| Voltage AC | 530 VAC |
| Rated Frequency | 50-60 Hz |
| Rated Current | 8 A (50°C) |
| Ripple Current | 8 A (50°C) |
| Rated Temperature | 50°C |
| Temperature Range | -25/+100°C |
| Climate Category | 25/100/21 |
| Test Voltage DC (P to P) | 2250 VDC |
| Test Voltage DC (P to E) | 3000 VDC |
| Max Power Loss | 3 W (25°C 50 Hz) |
| Leakage Current | 11 mA |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Bulk |
| Packaging Quantity | 1 |
| Typical Component Weight | 800 g |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.