

## LDBAA2330GC5N0

Aliases (DBAA2330GC5N0)

LDB, Film, Metallized PPS Stacked, General Purpose, 0.033 uF, 2%, 16 VDC, 125°C, 1.1 mm, 1206 / 3216



Click [here](#) for the 3D model.

### General Information

Series	LDB
Dielectric	Metallized PPS Stacked
Style	SMD Chip
RoHS	Yes
Typical Component Weight	0.06 g
Shelf Life	104 Weeks
MSL	3

### Dimensions

L	3.3mm +0.3/-0.1mm
W	1.7mm +/-0.2mm
T	1.1mm MAX
B	0.4mm +0.5/-0.3mm
Case Code (EIA / mm)	1206 / 3216

### Packaging Specifications

Packaging	T&R
Packaging Quantity	3000

### Specifications

Capacitance	0.033 uF
Tolerance	2%
Voltage DC	16 VDC
Temperature Range	-55/+125°C
Rated Temperature	125°C
Dissipation Factor	0.6% 1kHz
Insulation Resistance	3 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.