



Click [here](#) for the 3D model.

General Information

Series	LDE
Dielectric	Metallized PEN Stacked
Style	SMD Chip
Features	Automotive Grade
RoHS	Yes
Qualifications	AEC-Q200
Typical Component Weight	0.667 g
Shelf Life	104 Weeks
MSL	3

Dimensions

L	7.3mm +/-0.4mm
W	6.1mm +/-0.4mm
T	5.1mm MAX
B	0.4mm +0.5/-0.3mm
Case Code (EIA / mm)	2824 / 7260

Packaging Specifications

Packaging	T&R
Packaging Quantity	1500

Specifications

Capacitance	1.8 uF
Tolerance	10%
Voltage DC	63 VDC
Voltage AC	40 VAC
Temperature Range	-55/+125°C
Rated Temperature	125°C
Dissipation Factor	0.8% 1kHz
Insulation Resistance	222.2 MOhms
Max dV/dt	100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.