



Click [here](#) for the 3D model.

General Information

Series	MPLCG
Style	SMD Molded
Core	Metal Composite
Description	Shielded, Surface Mount Inductor
Features	Large Current Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Dimensions	
L	7.5mm MAX
W	6.7mm +/-0.2mm
T	3mm MAX
G	3.2mm +/-0.2mm

Packaging Specifications	
Typical Component Weight	650 mg
Packaging	T&R, 380mm
Packaging Quantity	2000

Specifications	
Inductance	1 uH (0.1 MHz)
Inductance Tolerance	20%
Rated Current	11.9 A (Irms, 40C Rise By Self Heating)
Saturation Current	11.3 A (Isat, 20% Drop In Inductance)
Temperature Range	-40/+125°C
Rated Temperature	120°C
Shielded	Yes
DC Resistance	9 mOhms
DC Resistance	9 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.