




YAGEO, PE Wide Terminal, Metal, SMD Wide Termination, 10 mOhms, 1%, 0612 / 1632



General Information	
Supplier	YAGEO
Series	PE Wide Terminal
Style	SMD Wide Termination
Description	Automotive Grade Metal Current Sensor - Low TCR Chip Resistor, wide terminal
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
AEC-Q200	Yes
Case Code (EIA / mm)	0612 / 1632

Click here for the 3D model.

Dimensions	
L	1.6mm +/-0.2mm
W	3.2mm +/-0.2mm
Т	0.6mm +/-0.15mm
B1	0.3mm +/-0.15mm
B2	0.3mm +/-0.15mm

T&R, 178mm

Packaging Specifications

Packaging

Specifications	
Resistance	10 mOhms
Resistance Tolerance	1%
Power	1W (70C)
Temp. Coefficient	-/+100 ppm/C
Temperature Range	-55/+155°C
Voltage DC	0.1 V (Max Continuous Voltage at Full Rated Power)
Voltage DC	0.1 V

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO