

PHE426JR8120JR06L2

Aliases (F426RP126J300C, PHE426JR8120JR06R06L2)

Not for New Design

PHE426/F426, Film, Metallized Polypropylene, General Purpose, 12 uF, 5%, 300 VDC, 85°C, 37.5 mm



Click [here](#) for the 3D model.

General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	30.96 g
Notes	Series Replaced by R75.

Dimensions

L	41mm MAX
H	38mm MAX
T	21mm MAX
S	37.5mm +/-0.5mm
LL	6mm NOM
F	1mm NOM

Packaging Specifications

Packaging	Tray
Packaging Quantity	84

Specifications

Capacitance	12 uF
Tolerance	5%
Voltage DC	300 VDC, 222 VDC (105C)
Voltage AC	160 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	2.5 GOhms
Max dV/dt	40 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.