

## PHE426MD6220JR06L2

Aliases (F426DH224J630C, PHE426MD6220JD14R06L2)

Not for New Design

PHE426/F426, Film, Metallized Polypropylene, General Purpose, 0.22 uF, 5%, 630 VDC, 85°C, 22.5 mm



Click [here](#) for the 3D model.

### General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	4.016 g
Notes	Series Replaced by R75.

### Dimensions

L	26mm MAX
H	16mm MAX
T	8mm MAX
S	22.5mm +/-0.4mm
LL	6mm NOM
F	0.8mm NOM

### Packaging Specifications

Packaging	Tray
Packaging Quantity	186

### Specifications

Capacitance	0.22 uF
Tolerance	5%
Voltage DC	630 VDC, 466 VDC (105C)
Voltage AC	250 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.1% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	200 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.