



Click [here](#) for the 3D model.

#### General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	26.65 g
Notes	Series Replaced by R75.

#### Dimensions

L	41mm MAX
H	36mm MAX
T	19mm MAX
S	37.5mm +/-0.5mm
LL	6mm NOM
F	1mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	91

#### Specifications

Capacitance	2.7 uF
Tolerance	5%
Voltage DC	630 VDC, 466 VDC (105C)
Voltage AC	250 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	11.1111 GOhms
Max dV/dt	80 V/us
Inductance	6 nH