
PHE840EF7220KF15R06L2

Aliases (F840FS225K300C)
Not for New Design
Recommended Replacement Series R46 X2 310 VAC
PHE840E/F840, Film, Metallized Polypropylene, Safety, 2.2 uF, 10%, 760 VDC, 300 VAC (X2), 105°C, 27.5 mm



Click here for the 3D model.

General Information	
Series	PHE840E/F840
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
Typical Component Weight	18.44 g
Notes	Not for new design – the replacement series is: R46 X2 310VAC.

Dimensions	
L	31.5mm MAX
H	29mm MAX
T	19mm MAX
S	27.5mm +/-0.4mm
LL	6mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	117

Specifications	
Capacitance	2.2 uF
Tolerance	10%
Voltage DC	760 VDC
Voltage AC	300 VAC (X2)
Temperature Range	-55/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.8% 10kHz
Insulation Resistance	4.5454 GOhms
Max dV/dt	100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO