



Click [here](#) for the 3D model.

General Information

Series	PHE850/F850
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	Y2
Qualifications	ENEC, UL, cUL
Typical Component Weight	0.887 g
Notes	Series Replaced by R41

Specifications

Capacitance	4,700 pF
Tolerance	10%
Voltage DC	1250 VDC
Voltage AC	300 VAC (Y2)
Temperature Range	-55/+110°C
Rated Temperature	110°C
Dissipation Factor	0.15% 1kHz, 0.2% 10kHz, 0.6% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	100 V/us

Dimensions

L	13mm MAX
H	11mm MAX
T	5mm MAX
S	10mm +/-0.4mm
LL	17mm NOM
F	0.6mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	800