



Click [here](#) for the 3D model.

#### General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	21.72 g
Notes	Series Replaced by R75.

#### Dimensions

L	31.5mm MAX
H	29mm MAX
T	19mm MAX
S	27.5mm +/-0.4mm
LL	6mm NOM
F	0.8mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	117

#### Specifications

Capacitance	8.2 uF
Tolerance	10%
Voltage DC	250 VDC, 185 VDC (105C)
Voltage AC	160 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	3.6585 GOhms
Max dV/dt	50 V/us
Inductance	6 nH