

## PHE426KB5680JR06

Aliases (F426BD683J400C, PHE426KB5680JB04R06)

Not for New Design

PHE426/F426, Film, Metallized Polypropylene, General Purpose, 0.068 uF, 5%, 400 VDC, 85°C, 15 mm



Click [here](#) for the 3D model.

### General Information

|                          |                          |
|--------------------------|--------------------------|
| Series                   | PHE426/F426              |
| Dielectric               | Metallized Polypropylene |
| Style                    | Radial                   |
| Features                 | Pulse                    |
| RoHS                     | Yes                      |
| Termination              | Tinned Wire              |
| Lead                     | Wire Leads               |
| Typical Component Weight | 1.368 g                  |
| Notes                    | Series Replaced by R75.  |

### Dimensions

|    |               |
|----|---------------|
| L  | 18mm MAX      |
| H  | 10.5mm MAX    |
| T  | 5.5mm MAX     |
| S  | 15mm +/-0.4mm |
| LL | 6mm NOM       |
| F  | 0.8mm NOM     |

### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 1000      |

### Specifications

|                       |                          |
|-----------------------|--------------------------|
| Capacitance           | 0.068 uF                 |
| Tolerance             | 5%                       |
| Voltage DC            | 400 VDC, 296 VDC (105C)  |
| Voltage AC            | 220 VAC                  |
| Temperature Range     | -55/+105°C               |
| Rated Temperature     | 85°C                     |
| Dissipation Factor    | 0.05% 1kHz, 0.25% 100kHz |
| Insulation Resistance | 100 GOhms                |
| Max dV/dt             | 200 V/us                 |
| Inductance            | 6 nH                     |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.