



Click [here](#) for the 3D model.

**General Information**

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	5.444 g
Notes	Series Replaced by R75.

Dimensions	
L	26mm MAX
H	18.5mm MAX
T	9mm MAX
S	22.5mm +/-0.4mm
LL	6mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	308

Specifications	
Capacitance	0.68 uF
Tolerance	20%
Voltage DC	400 VDC, 296 VDC (105C)
Voltage AC	220 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.1% 10kHz
Insulation Resistance	44.1176 GOhms
Max dV/dt	150 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.