



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|------------------------------|
| Series | R53B |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | Automotive Grade, EMI Safety |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Safety Class | X2 |
| Qualifications | ENEC, UL, cUL, CQC, AEC-Q200 |
| THB Performance | Yes |
| Typical Component Weight | 11.1 g |
| Construction | Parallel |

Dimensions

| | |
|----|------------------|
| L | 32mm +0.5/-0.7mm |
| H | 22mm +0.3/-0.7mm |
| T | 13mm +0.3/-0.7mm |
| S | 27.5mm +/-0.4mm |
| LL | 25mm +2/-1mm |
| F | 0.8mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | Pizza, Box |
| Packaging Quantity | 288 |

Specifications

| | |
|-----------------------|--------------|
| Capacitance | 1.2 uF |
| Tolerance | 10% |
| Voltage DC | 800 VDC |
| Voltage AC | 350 VAC (X2) |
| Temperature Range | -40/+125°C |
| Rated Temperature | 110°C |
| Dissipation Factor | 0.3% 1kHz |
| Insulation Resistance | 8.333 GOhms |
| Max dV/dt | 150 V/us |