


[Click here for the 3D model.](#)

#### General Information

Hersteller	YAGEO
Gruppe	RC
Typ	SMD Chip
Beschreibung	Standard Thick Film Chip Resistors
RoHS	Yes
Terminierung	Tin
AEC-Q200	No
Haltbarkeit	104 Weeks
Chip Size / Footprint	2512 / 6332

#### Dimensions

L	6.35mm +/-0.1mm
W	3.1mm +/-0.15mm
T	0.55mm +/-0.1mm
B1	0.6mm +/-0.2mm
B2	0.6mm +/-0.2mm

#### Specifications

Widerstand (Widerstände)	2.37 Ohms
Widerstandstoleranz	1%
Leistung	1W (70C)
Temperaturkoeffizient (Widerstände)	-/+200 ppm/C
Temperaturbereich	-55/+155°C
Gleichspannung	200 V (Max Continuous Voltage at Full Rated Power), 500 Max Over Voltage, 500 Dielectric Withstanding Voltage

#### Packaging Specifications

Verpackung	T&R, 178mm
------------	------------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.