
## RP1206BRD07301KL

YAGEO, RP, Thin Film, SMD Chip, 301 kOhms, 0.1%, 1206





General Information	
Supplier	YAGEO
Series	RP
Style	SMD Chip
Chip Size	1206
Description	Automotive Grade Thin Film Chip
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
AEC-Q200	Yes

Click here for the 3D model.

Dimensions		
L	3.1mm +/-0.1mm	
W	1.6mm +/-0.1mm	
Т	0.55mm +/-0.1mm	
B1	0.45mm +/-0.2mm	
B2	0.4mm +/-0.2mm	

Packaging Specifications	
Packaging	T&R, 178mm, Paper Tape
Packaging Quantity	5000

Specifications	
Resistance	301kOhms
Resistance Tolerance	0.1%
Power	0.25 W (70C)
Temp. Coefficient	-/+25 ppm/C
Temperature Range	-55/+155°C
Voltage DC	200 V (Max Continuous Voltage at Full Rated Power), 400 Max Over Voltage
Voltage DC	200 V

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO