


RL2512FK-070R022L

Aliases (RL2512FK070R022L) YAGEO, RL, Thick Film, SMD Chip, 22 mOhms, 1%, 2512 / 6332



General Information	
Supplier	YAGEO
Series	RL
Style	SMD Chip
Description	Current Sensor resistor
RoHS	Yes
Termination	Tin
AEC-Q200	No
Case Code (EIA / mm)	2512 / 6332

Click here for the 3D model.

Dimensions	
L	6.35mm +/-0.1mm
W	3.2mm +/-0.15mm
Т	0.55mm +/-0.1mm
B1	0.6mm +/-0.2mm
B2	0.5mm +/-0.2mm

Packaging Specifications		
Packaging	T&R, 178mm	

Specifications	
Resistance	22 mOhms
Resistance Tolerance	1%
Power	1W (70C)
Temp. Coefficient	-/+1200 ppm/C
Temperature Range	-55/+155°C
Voltage DC	0.1 V (Max Continuous Voltage at Full Rated Power)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/03/2025 © 2006 - 2025 YAGEO