



## SBS9080-509T

Aliases (UDLSBS9080509T)

EOL: 11-30-2026 / Last time buy date: 05-29-2026

Common Mode Chokes - Signal, KEMET, SBS9080, SMD, Common Mode



Click [here](#) for the 3D model.

### General Information

Series	SBS9080
Style	SMD
RoHS	With Exemptions
SCIP Number	4da5c62f-a115-440c-bba8-0dc143ab9e3e
Miscellaneous	Withstanding Voltage: 125 VDC 1min Between Lines, Insulation Resistance: 10MΩ MIN (100 VDC Between Lines).

### Dimensions

L	9.7mm MAX
W	8.7mm MAX
T	5.4mm MAX
LL	1.5mm NOM
S	7.2mm MAX
S1	6.3mm NOM

### Specifications

Voltage DC	50 VDC
Temperature Range	-25/+50°C
DC Resistance	15 mΩ (per Line MAX)

### Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	1000
Typical Component Weight	900 mg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.