
SS24H-R05600-CH

Aliases (UAL24HR05600CH)

Obsolete

Recommended Replacement: SSR21NHS-M051200 or SSR21NHS-M07680

Common Mode Chokes - Power, KEMET, SS24V/H-CH, Through-Hole Bobbin, Common Mode, 0.06 H



General Information	
Series	SS24V/H-CH
Style	Through-Hole Bobbin
RoHS	Yes
Notes	EOL: Jun 30th 2026 Alternative PN SSR21NHS-M051200
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

Dimensions	
L	26mm MAX
T	26mm MAX
H	21mm MAX
LL	4mm +/-1mm
S	21mm +/-0.5mm
S1	15mm +/-0.5mm
F	0.8mm NOM

Specifications	
Voltage AC	250 VAC
Inductance	60 mH
Rated Current	500 mA
Temperature Range	-25/+120°C
DC Resistance	1.75 Ohms

Packaging Specifications	
Typical Component Weight	17.1 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO