
SSR21NV-05795

Aliases (UALN21V0579500)

Obsolete

Recommended Replacement: SSR21NV-M051350 or SSR21NV-M07890

Common Mode Chokes - Power, KEMET, SSR21NV/NH, Through-Hole Bobbin, Common Mode, 0.0795 H



Click here for the 3D model.

General Information	
Series	SSR21NV/NH
Style	Through-Hole Bobbin
Features	Compact Size, Light Weight, High Performance, Low DCR, High Impedance, Strong Inductance
RoHS	Yes
Notes	EOL: Jun 30th 2026 Alternative PN SSR21NV-M051350
Miscellaneous	45 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions	
L	22mm MAX
T	16mm MAX
H	27mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.25mm
F	0.8mm NOM

Specifications	
Voltage AC	250 VAC
Inductance	79.5 mH
Rated Current	500 mA
Temperature Range	-40/+120°C
DC Resistance	1.2 Ohms

Packaging Specifications	
Packaging	Tray
Packaging Quantity	450
Typical Component Weight	14.5 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO