



Click [here](#) for the 3D model.

General Information

Series	T490
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, MnO2, Molded, Consumer
RoHS	Yes
Termination	Tin
Typical Component Weight	58.6 mg
Shelf Life	156 Weeks
MSL	1

Dimensions	
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	1.2mm +/-0.1mm
A	1.2mm MIN
B	0.4mm +/-0.15mm
E	1.3mm REF
G	1.1mm REF
P	0.4mm REF
R	0.4mm REF
X	0.1mm +/-0.1mm REF

Specifications	
Capacitance	68 uF
Tolerance	20%
Voltage DC	6 VDC (40C), 3 VDC (85C), 1.2 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	40°C
Humidity	40C, 93% RH, 1000 Hours, No Load
Failure Rate	N/A
ESR	1 Ohms (100kHz 25C)
Ripple Current	274 mAmps (100kHz 25C), 246.6 mAmps (40C), 109.6 mAmps (125C)
Leakage Current	4.1 uA (5min 25°C)

Packaging Specifications	
Packaging	T&R, 178mm
Packaging Quantity	2000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.