



Click [here](#) for the 3D model.

### General Information

Series	T550
Dielectric	Polymer Tantalum
Style	Axial Hermetic
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a>
Termination	Solder Coated
Lead	Wire Leads
Construction	Hermetic
Typical Component Weight	3.63 g
Miscellaneous	Sleeved.
Notes	Dimensions Include Insulating Sleeve. When Supplied On T&R Or Ammo, Lead Length Is Determined By Taping Specification.
Shelf Life	156 Weeks

### Dimensions

D	7.34mm +0.41/-0.38mm
L	17.42mm +/-0.79mm
L2	20.88mm MAX
LL	38.1mm +/-6.35mm
F	0.64mm +/-0.05mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	20

### Specifications

Capacitance	82 uF
Tolerance	20%
Voltage DC	75 VDC (85C), 58.5 VDC (105C), 86.25 VDC (85C Surge)
Temperature Range	-55/+105°C
Rated Temperature	85°C
Life	2000 Hrs
Humidity	40C, 60% RH
Dissipation Factor	6% 120Hz 25C
Failure Rate	N/A
ESR	220 mOhm (100kHz 25C)
Ripple Current	1110 mAmps (40kHz 85C)
Leakage Current	57.6 uA (5min 25°C)
Testing and Reliability	25C +/-5C, 10 cycles, after constant voltage conditioning (KEMET standard)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.