

T593V686M035APE100

T593, Tantalum, Polymer Tantalum, Commercial Grade, 68 uF, 20%, 35 VDC, SMD, Polymer, Molded, High Humidity, 100 mOhms, 2 mm, 2817 / 7343



Click [here](#) for the 3D model.

General Information

Series	T593
Dielectric	Polymer Tantalum
Style	SMD Chip
Description	SMD, Polymer, Molded, High Humidity
Features	High Humidity
RoHS	Yes
Termination	Nickel Palladium Gold
Typical Component Weight	274.3 mg
Shelf Life	52 Weeks
MSL	3

Dimensions

L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	1.9mm +/-0.1mm
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	1000

Specifications

Capacitance	68 uF
Tolerance	20%
Voltage DC	35 VDC (105C)
Temperature Range	-55/+105°C
Rated Temperature	105°C
Life	2000 Hrs (105C)
Humidity	85C, 85% RH, 1000 Hours, VR
Dissipation Factor	10% 120Hz 25C
Failure Rate	N/A
ESR	100 mOhms (100kHz 25C)
Ripple Current	2030 mA (rms, 100kHz 45C), 1421 mA (rms, 85C), 507.5 mA (rms, 105C)
Leakage Current	238 uA (5min 25°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.