


[Click here for the 3D model.](#)

#### General Information

Hersteller	KEMET
Gruppe	VC
Typ	Varistors
Typ	SMD Chip
Beschreibung	Surface Mount Varistors
Eigenschaften	Low Voltage
Terminierung	Nickel Tin
RoHS	With Exemptions
Zulassungen	IEC, AEC-Q200

#### Dimensions

L	2mm +/-0.25mm
W	1.25mm +/-0.2mm
T	1.05mm MAX
B	0.5mm +/-0.25mm
Chip Size / Footprint	0805 / 2012

#### Specifications

Gleichspannung	26 VDC (25C)
Wechselspannung	20 VAC
Temperaturbereich	-55/+125°C
Lagertemperaturbereich	-55/+150°C
Varistorspannung	33 VDC at 1mA
Klemmspannung	54 V
Klemmstrom	1A (8/20 us MAX)
Surge Strom	120 A (8/20 us MAX)
Energie	0.4 J (10/1000 us MAX)
Leistung	0.005 W (MAX)
Kapazitätsanzeige	290 pF (1kHz)

#### Packaging Specifications

Verpackung	T&R
Verpackungsmenge	3500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.