

Power Inductor

Automotive Grade

APSR Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

1. Automotive grade available
2. Plated terminals on the ferrite core, frameless can be low profile
3. Ferrite SMD Shielded Type
4. No thermal aging

Applications

1. Automotive Systems for Dashboard, CCD Module
2. Media player
3. Net working
4. Lighting, LCD Panel/TV

Product Information

Series	L (mm)	W (mm)	T (mm)	Inductance (μH)
APSR	5.2	5.0	2.2	1 ~ 150
	5.2	5.0	2.2	
	7.5	7.4	2.5	
	7.5	7.4	4.0	




APSR00080740 Series Specification

AEC-Q200

1 Scope: This specification applies to SMD Shielded Power Inductors

2 Part Numbering:




3 Rating:

Operating Temperature: - 40°C ~ + 125°C (Including self temp. rise)

Storage Temperature: - 40°C ~ + 125°C (For after the circuit board is mounted)

Storage Temperature: (on tape & reel): -20°C to +40°C; 75% RH max.

4 Marking:



Ex Marking : 100

Marking Color : Black


5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

APSR00080740 Series Specification

AEC-Q200

6 Configuration and Dimensions and Unit Weight:



Net Weight (grms)

SIZE CODE	Net Weight (grms)
080740	0.68(Typ.)

7 Electrical Characteristics:

Part No.	Inductance (uH)	Test Freq.	RDC (mΩ)Max.	Isat(A) Max(Typ)	Irms (A)	Tolerance	Marking
APSR000807401R0□00	1	100kHz,1V	6.38	8.0(12.0)	9	T	1R0
APSR000807401R5□00	1.5	100kHz,1V	8.64	7.0(10.0)	8	T	1R5
APSR000807401R8□00	1.8	100kHz,1V	9.6	6.5(8.6)	7.92	T	1R8
APSR000807402R5□00	2.5	100kHz,1V	13.6	4.8(7.2)	7.4	T	2R5
APSR000807403R3□00	3.3	100kHz,1V	17.8	3.9(6.8)	6.7	T	3R3
APSR000807404R7□00	4.7	100kHz,1V	26.6	3.5(4.6)	4.9	M,T	4R7
APSR000807405R6□00	5.6	100kHz,1V	29	3.3(4.1)	4.6	M,T	5R6
APSR000807406R8□00	6.8	100kHz,1V	34	3.2(3.9)	3.9	M,T	6R8
APSR00080740100□00	10	100kHz,1V	55.6	2.5(3.4)	3.25	M,T	100
APSR00080740150□00	15	100kHz,1V	71.4	2.1(3.0)	2.7	M,T	150
APSR00080740220□00	22	100kHz,1V	98.1	1.7(2.4)	2.4	M,T	220
APSR00080740330□00	33	100kHz,1V	140	1.4(2.0)	1.9	M,T	330
APSR00080740470□00	47	100kHz,1V	217	1.2(1.7)	1.48	M,T	470
APSR00080740560□00	56	100kHz,1V	260	1.0(1.5)	1.33	M,T	560
APSR00080740680□00	68	100kHz,1V	310	0.95(1.36)	1.2	M,T	680
APSR00080740820□00	82	100kHz,1V	360	0.90(1.20)	1.12	M,T	820
APSR00080740101□00	100	100kHz,1V	480	0.85(1.12)	0.95	M,T	101
APSR00080740121□00	120	100kHz,1V	560	0.75(1.00)	0.89	M,T	121
APSR00080740151□00	150	100kHz,1V	710	0.65(0.92)	0.82	M,T	151

NOTE: □-tolerance M=±20% / T=±30%

1.Operating temperature range - 4 0 °C ~ 1 2 5 °C(Including self - temperature rise)

2.Isat for Inductance drop 35% from its value without current.


3.Irms for a 40°C temperature rise from 25°C ambient.

4.The actual use current is suggested not to be out of Isat*80%

★ Rated DC Current : The less value whith is Isat or Irms.

8 APSR00080740 Series

8.1 Construction:



8.2 Material List:


No	Part	Material
1	Core	Ferrite
2	Wire	Copper Wire
3	Pin Base	C1100

APSR00080740 Series Specification

AEC-Q200

9 Reliability Of Ferrite Wire Wound Power Inductor


1-1.Mechanical Performance

No	Item	Specification	Test Method
1-1-1	Board Flex	The forces applied on the right conditions must not damage the terminal electrode and the ferrite	Refer to AEC-Q200-005 Test device shall be soldered on the substrate Substrate Dimension: 100x40x1.6mm Deflection: 2.0mm Keeping Time: 60sec 
1-1-2	Resistance to Soldering Heat	Appearance: No damage Inductance change shall be within $\pm 10\%$.	Refer to MIL-STD-202 Method 210 Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free) Solder Temperature: 250 ± 5 °C Immersion Time: 10 ± 1 sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Refer to J-STD-002 Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free) Solder Temperature: 245 ± 5 °C (Pb-Free) Immersion Time: 4 ± 1 sec
1-1-4	Terminal Strength Test	Appearance: No damage	Refer AEC-Q200-006 Soldered on PCB for testing as fig. Force : 1.8kg Keeping Time: 60 seconds.
1-1-5	Resistance to Solvent	There must be no change in appearance or obliteration of marking	Refer to MIL-STD-202 Method 215 Inductors must withstand 6 minutes of alcohol or water Sample Size : 15 pcs
1-1-6	Vibration	Appearance: No damage Inductance change shall be within $\pm 10\%$.	Refer MIL-STD-202 Method 204 Vibration waveform: Sine waveform Vibration frequency: 10Hz~2000Hz Vibration acceleration: 5g Sweep rate: 0.764386octave/minute Duration of test: 12 cycles each of 3 orientations, 20 minutes for each cycle Vibration axes: X, Y & Z

1-2.Environmental Performance

No	Item	Specification	Test Method
1-2-1	Temperature Cycle	Appearance: No damage Inductance change shall be within $\pm 30\%$	Refer to JESD Method JA-104 Total cycles: 1000 cycles Temperature Cycling Test Conditions : -40 to +125 °C -40 °C Soak Mode Condition : 30 minutes 125 °C Soak Mode Condition : 30 minutes Measured after exposure in the room condition for 24hrs
1-2-2	Biased Humidity Resistance		Refer to MIL-STD-202 Method 103 Temperature: 85 ± 2 °C Relative Humidity:85% / Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-3	High Temperature Exposure (Storage)		Refer to MIL-STD-202 Method 108 Temperature: 125 ± 3 °C Applied Current: Rated Current /Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-4	Operational Life		Refer to MIL-STD-202 Method 108 Temperature: 85 ± 3 °C Applied Current : Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs

Reflow Soldering Profile



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升温區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	Above 217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	—	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	—
實際時間 Time result	—	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	—


NOTE :

1. Re-flow possible times : within 2 times
2. Nitrogen adopted is recommended while in re-flow
3. Products can only be soldered with reflow

10 Packaging:

10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



10.2 Packaging Quantity

TYPE	PCS/REEL
080740	1000

10.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
080740	330	100	13	16


10 Packaging:

10.4 Tape Dimensions in mm



TYPE	A0	B0	K0	D	E	W	P	P0	P2
080740	7.6	9.0	4.3	1.55	1.75	16	12	4	2

11 Recommended Land Pattern:



Dimensions in mm

TYPE	A	B	C
080740	1.5	5.4	2.8

12 Note:


1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.

APSR00080740 Series Specification



AEC-Q200

13 Graph:



APSR000807401R0□00





APSR000807401R5□00



APSR000807401R8□00




APSR000807402R5□00





13 Graph:



APSR000807403R3□00





APSR000807404R7□00



APSR000807405R6□00





APSR000807406R8□00





13 Graph:



APSR00080740100□00





APSR00080740150□00



APSR00080740220□00





APSR00080740330□00





13 Graph:



APSR00080740470□00





APSR00080740560□00



APSR00080740680□00





APSR00080740820□00





13 Graph:

APSR00080740101□00



APSR00080740121□00



APSR00080740151□00

