

RF Inductor

Automotive Grade

AWLS Series



Overview

Wire-wound RF inductors are electronic components designed to store energy in a magnetic field when electrical current passes through them. They are constructed by winding a conductive wire (usually copper or gold-plated) around a core material such as air, ceramic, or ferrite.

This configuration allows them to provide high inductance values with minimal power loss, especially at high frequencies.

Benefits

1. High Q-Factor (Quality Factor)
2. Wide Frequency Range
3. Low Signal Loss
4. High Current Handling
5. Can maintain excellent thermal stability at different temperatures

Applications

1. Automotive Electronics: infotainment systems, ADAS, and car keyless entry systems.
2. Industrial and Medical Equipmen: RFID systems and medical imaging equipment.
3. Data Centers and Networking
4. Consumer Electronics

Product Information

Series	Size Code (JIS/EIA)	Inductance (nH)
AWLS	1.0x0.6/0402	18 ~ 39000
	1.6x1.1/0603	
	2.4x1.7/0805	
	3.0x2.5/1008	




AWLS00100606 Series Specification

AEC-Q200

1 Scope: This specification applies to Wire Wound Ferrite Chip Inductors

2 Part numbering:



3 Rating:

Operating Temperature: $-55^{\circ}\text{C} \sim 125^{\circ}\text{C}$
(Including self - temperature rise)

Storage Temperature: $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$
(The storage temperature range is for after the assembly)

4 Marking:

No Marking


5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80% RH

AWLS00100606 Series Specification

AEC-Q200

6 Configuration and Dimensions and Unit Weight:



Net Weight (grms)

SIZE CODE	Net Weight (grms)
100606	0.001 (typ.)

7 Electrical Characteristics:

Part No.	Inductance (nH)	L/Q Test Freq. (MHz)	Q Typ.	SRF (MHz)Typ.	RDC (Ω)Max.	I _{rms} (mA)Max.	Tolerance (±%)
AWLS0010060618N□00	18	100	10	2600	0.055	1600	5,10
AWLS0010060620N□00	20	100	10	2600	0.05	1600	5,10
AWLS0010060622N□00	22	100	10	2500	0.072	1300	10
AWLS0010060633N□00	33	100	10	2300	0.06	1400	5,10
AWLS0010060636N□00	36	100	10	2300	0.092	1000	5,10
AWLS0010060639N□00	39	100	10	2200	0.15	830	5,10
AWLS0010060651N□00	51	100	10	1930	0.07	1100	10
AWLS0010060656N□00	56	100	10	1900	0.125	900	10
AWLS0010060672N□00	72	100	10	1650	0.1	900	5,10
AWLS0010060678N□00	78	100	10	1600	0.19	850	5,10
AWLS00100606R10□00	100	100	9	1400	0.16	900	10
AWLS00100606R14□00	140	50	11	1220	0.26	540	5,10
AWLS00100606R16□00	160	50	11	1200	0.32	560	5,10
AWLS00100606R18□00	180	50	11	1150	0.33	560	5,10
AWLS00100606R20□00	200	50	11	1000	0.44	400	5,10
AWLS00100606R22□00	220	50	11	1150	0.53	380	5,10
AWLS00100606R25□00	250	25	11	900	0.36	520	5,10
AWLS00100606R27□00	270	25	11	860	0.55	360	10
AWLS00100606R30□00	300	25	11	860	0.41	420	5,10
AWLS00100606R33□00	330	7.9	11	820	0.68	350	5,10
AWLS00100606R36□00	360	7.9	11	810	0.575	360	5,10
AWLS00100606R39□00	390	7.9	11	760	0.89	300	5,10
AWLS00100606R42□00	420	7.9	11	700	1.1	340	5,10
AWLS00100606R47□00	470	7.9	11	650	0.73	310	5,10
AWLS00100606R56□00	560	7.9	11	600	1.1	200	5,10

NOTE: □-tolerance J=±5% / K=±10%

1. Operating temperature range — 55°C ~ 125°C(Including self - temperature rise)

2. L/Q Test OSC @200mV.


3. I_{rms} for a 15°C temperature rise from 25°C amAient.

AWLS00100606 Series Specification

AEC-Q200

8 AWLS00100606 Series

8.1 Construction:



8.2 Material List:


NO	PART	MATERIAL
1	WIRE	Grade 180
2	EPOXY	UV GLUE
3	CORE	FERRITE CORE
4	TERMINAL	Ag/Cu/Ni/Sn

AWLS00100606 Series Specification

AEC-Q200


9 Reliability Of Ferrite Wire Wound Chip Inductor/FERRITE SERIES

1-1.MECHANICAL PERFORMANCE

No	Item	Specification	Test Method
1-1-1	Board Flex	The forces applied on the right conditions must not damage the terminal electrode and the ferrite.	Test device shall be soldered on the substrate Substrate Dimension: 100x40x1.6mm Deflection: 2.0mm Keeping Time: 60 sec 
1-1-2	Terminal Strength	The chip must not damage the terminal electrode and the ferrite.	Refer to AEC-Q200-006 Test device shall be soldered on the substrate Force 0.5lbs for 60±1 seconds for 0201 series Force 1lbs for 60±1 seconds for 0402 series Force 2lbs for 60±1 seconds for 0603 series Force 1.8Kg for 60±1 seconds for the other series.
1-1-3	Solderability	The electrodes shall be at least 95% covered with new solder coating.	Pre-heating: 150℃, 1min Solder Composition: Sn/3.0Ag/0.5Cu Solder Temperature: 245±5℃ Immersion Time: 4±1sec
1-1-4	Resistance to Soldering Heat	Appearance:No damage Inductance change shall be within ±10%. Q change:within±30% of initial value	Pre-heating: 150℃, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260±5℃ Immersion Time: 10±1sec
1-1-5	Resistance to Solvents	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.
1-1-6	Mechanical Shock	The forces applied on the right conditions must not damage the terminal electrode and the ferrite.	Pulse shape : Half-sine waveform Impact acceleration : 100 g Pulse duration : 6 ms Number of shocks : 18 shocks (3 shocks for each face) Orientation : Bottom, top, left, right, front and rear faces
1-1-7	Vibration	Appearance:No damage Inductance change shall be within ±10%. Q change:within±30% of initial value	Vibration waveform: Sine waveform Vibration frequency: 10Hz~2000Hz Vibration acceleration: 5g Sweep rate: 0.764386octave/minute Duration of test: 12 cycles each of 3 orientations 20 minutes for each cycle Vibration axes: X, Y & Z

1-2.ENVIRONMENTAL PERFORMANCE

No	Item	Specification	Test Method
1-2-1	High Temperature Exposure (Storage)	Appearance:No damage (for microscope of CASTOR MZ-45 20X)Inductance change shall be within ±10%. Q change:within±30% of initial value	Temperature: 125±3℃ Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-2	Low Temperature Exposure (Storage)		Temperature: -55±3℃ Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-3	Biased Humidity		Temperature: 85±2℃ Relative Humidity: 85% Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-4	Temperature Cycling		Total cycles: 1000 cycles Temperature Cycling Test Conditions : -55 to +125 °C Soak Mode Condition : 30 minutes Measured after exposure in the room condition for 24hrs
1-2-5	Operational Life		Temperature: 125±2℃ Applend Current : Rated Current Time: 1000± 24 hrs Measured after exposure in the room condition for 24hrs
1-2-6	ESD		Test mode : Contact Discharge Discharge level : ±6KV, Discharge interval : 1 second Polarity of the output voltage : Positive and negative Number of discharge : Discharge +/- for 1 time for the 2 test points.
			Test Mode : Air Discharge Discharge level : ±12KV, ±16KV, ±25KV Discharge interval : <5 seconds Polarity of the output voltage : Positive and negative Number of discharge : Discharge +/- for 1 time for the 1~2 test points.



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	Above 217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	-	60 ~ 180 sec	60 ~ 150 sec	5~10 sec	-
實際時間 Time result	-	75 ~ 100 sec	90 ~ 120 sec	10 sec	-

NOTE:

- 1.Re-flow possible times : within 3 times
- 2.Nitrogen adopted is recommends while in re-flow
- 3.Products can only be soldered with reflow


AWLS00100606 Series Specification

AEC-Q200

10 Packaging:

10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



10.2 Packaging Quantity

TYPE	PCS/REEL
100606	4000

10.3 Reel Dimensions



Dimensions in mm


TYPE	A	B	C	D
100606	178±1	60±0.5	12±0.5	1.5±0.5

AWLS00100606 Series Specification

AEC-Q200


10 Packaging:

10.4 Tape Dimensions in mm



TYPE	A	B	C	D	E	F	G	T	K
100606	8.0	0.67	2	1.20	3.5	1.75	2	0.75	0.59

11 Recommended Land Pattern:



Dimensions in mm

TYPE	H(In/mm)	I(In/mm)	J(In/mm)
100606	0.025/0.65	0.14/0.38	0.017/0.44

12 Note:


- Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- Do not knock nor drop.
- All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- The storage period is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% RH or less).
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- The moisture sensitivity level (MSL) of products is classified as level 1.

AWLS00100606 Series Specification


AEC-Q200

13 Graph:


AWLS0010060618N□00




AWLS0010060620N□00




AWLS0010060622N□00




AWLS0010060633N□00




AWLS0010060636N□00




AWLS0010060639N□00



AWLS0010060651N□00











AWLS0010060656N□00



AWLS00100606 Series Specification


AEC-Q200




AWLS00100606 Series Specification

AEC-Q200


AWLS00100606R25□00




AWLS00100606R27□00




AWLS00100606R30□00




AWLS00100606R33□00




AWLS00100606R36□00




AWLS00100606R39□00



AWLS00100606R42□00



AWLS00100606R47□00



AWLS00100606 Series Specification

AEC-Q200

