


BP3Y00101010XXXM00 Series Specification

1 Scope: This specification applies to large current and low RDC SMD power inductor.

2 Part Numbering:




3 Rating:

Operating temperature range: $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$ (Including self - temperature rise)

Storage condition: $-20^{\circ}\text{C} \sim 40^{\circ}\text{C}$; 75%RH Max

4 Marking:



Marking color : White

Ex Marking XXX

5 Material List:

NO	Part	Material
1	Copper Wire	EIAIW (200°C)
2	Core	Carbonyl iron powder
3	coating	Paint Gray (127# matte)
4	Solder	Sn96.5-Ag3.0-Cu0.5
5	Ink	PIC-1083B-白
6	EPOXY	M02-039-AU(6461HF)
7	Clip	C1100


6 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80% RH


BP3Y00101010XXM00 Series Specification

7 Configuration and Dimensions:

TOP VIEW



SIDE VIEW



BOTTOM VIEW



Product appearance



Part No.	A	B	C	D	E
BP3Y00101010R22M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y00101010R45M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y00101010R68M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010101R0M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010101R5M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010102R2M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010103R3M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010104R7M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010105R6M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010106R8M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y001010108R2M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y00101010100M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3
BP3Y00101010150M00	11.8 max	11.8max	10.0Max	8.6±0.3	2.2±0.3

8 Electrical Characteristics:



Part No.	Inductance (uH)	Test Freq.	Tolerance (±%)	Irms (A)Typ.	Isat (A)Typ.	RDC (mΩ)Max	Marking
BP3Y00101010R22M00	0.22	100kHz,1.0V	20	55	130	0.55	R22
BP3Y00101010R45M00	0.45	100kHz,1.0V	20	50	90	0.80	R45
BP3Y00101010R68M00	0.68	100kHz,1.0V	20	45	80	1.0	R68
BP3Y001010101R0M00	1.0	100kHz,1.0V	20	40	68	1.3	1R0
BP3Y001010101R5M00	4.5	100kHz,1.0V	20	35	62	1.9	1R5
BP3Y001010102R2M00	2.2	100kHz,1.0V	20	30	70	3.1	2R2
BP3Y001010103R3M00	3.3	100kHz,1.0V	20	25	48	4.3	3R3
BP3Y001010104R7M00	4.7	100kHz,1.0V	20	20	28	6.7	4R7
BP3Y001010105R6M00	5.6	100kHz,1.0V	20	21	27	7.4	5R6
BP3Y001010106R8M00	6.8	100kHz,1.0V	20	18	22	9.4	6R8
BP3Y001010108R2M00	8.2	100kHz,1.0V	20	17	20	14.5	8R2
BP3Y00101010100M00	10	100kHz,1.0V	20	15	19	16.5	100
BP3Y00101010150M00	15	100kHz,1.0V	20	13	16	21.5	150

Note:

- 1.Ambient + temperature rise range — 40°C ~ 125°C(Including self - temperature rise)
- 2.Isat for Inductance drop 30% from its value without current.
- 3.Irms for a 40°C temprature rise from 25°C ambient.
- 4.The part temperature (ambient + temp rise) should not exceed 125°C under worst case operating conditions.
Circuit design125°C under worst case operating conditions. Component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

BP3Y00101010XXM00 Series Specification

9 Reliability verification conditions

Item	Specification	Conditions															
Solderability	More than 90% of the terminal electrode should be covered with solder.	 Unit: Second															
Solder Heat Resistance	Inductance within $\pm 20\%$ of initial value. No disconnection or short circuit. The appearance shall not break.	 Unit: Second															
Heat resistance	Inductance within $\pm 20\%$ of initial value. No disconnection or short circuit. The appearance shall not break.	After 1000 hours in $125\pm 5^\circ\text{C}$ and 2 hour drying under normal condition.															
Cold resistance	Inductance within $\pm 20\%$ of initial value. No disconnection or short circuit. The appearance shall not break.	After 1000 hours in $-40\pm 5^\circ\text{C}$ and 2 hour drying under normal condition.															
Thermal shock	Inductance within $\pm 20\%$ of initial value. No disconnection or short circuit. The appearance shall not break.	After 100 cycles of following condition. <table border="1"> <thead> <tr> <th>Step</th><th>Temperature ($^\circ\text{C}$)</th><th>Times (min.)</th></tr> </thead> <tbody> <tr> <td>1</td><td>$-40\pm 5^\circ\text{C}$</td><td>30</td></tr> <tr> <td>2</td><td>Room Temperature</td><td>Within 3</td></tr> <tr> <td>3</td><td>$125\pm 5^\circ\text{C}$</td><td>30</td></tr> <tr> <td>4</td><td>Room Temperature</td><td>Within 3</td></tr> </tbody> </table>	Step	Temperature ($^\circ\text{C}$)	Times (min.)	1	$-40\pm 5^\circ\text{C}$	30	2	Room Temperature	Within 3	3	$125\pm 5^\circ\text{C}$	30	4	Room Temperature	Within 3
Step	Temperature ($^\circ\text{C}$)	Times (min.)															
1	$-40\pm 5^\circ\text{C}$	30															
2	Room Temperature	Within 3															
3	$125\pm 5^\circ\text{C}$	30															
4	Room Temperature	Within 3															
Humidity Resistance	Inductance within $\pm 20\%$ of initial value. No disconnection or short circuit. The appearance shall not break.	After 1000 hours in $40\pm 2^\circ\text{C}$ and 90 to 95% humidity , and 2 hour drying under normal condition.															
Vibration Test	Inductance within $\pm 5\%$ of initial value and appearance shall not break.	After vibration for 1hour, In each of three orientations at sweep vibration (10~55~10Hz) with 1.52mm P-P Amplitudes.															

BP3Y00101010XXM00 Series Specification

10 Reflow Profile:






Figure 2. Hand Soldering



BP3Y00101010XXXM00 Series Specification


11 Packaging:

11.1 Reel Dimension



Type	A(mm)	B(mm)	C(mm)	D(mm)
13" x 24mm	24.5 ± 0.5	100 ± 2	13.5 ± 0.5	330

11.2 Tape Dimension



P/N	Ao(mm)	Bo(mm)	Ko(mm)	P(mm)	T(mm)	W(mm)	PCS/REEL
BP3Y00101010 SERIES	11.8 ± 0.1	11.8 ± 0.1	10.0 ± 0.1	20.0 ± 0.1	0.5 ± 0.05	24.0 ± 0.3	250

BP3Y00101010XXM00 Series Specification

13 Graph :

