

Power Inductor



BPCA Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

1. Ferrite SMD Shielded Type
2. Ultra High Current

Applications

1. Thin-screen TVs
2. LCDs
3. AV equipment
4. STBs
5. LED lights

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPCA	6.0	6.3	4.5	1 ~ 470
	7.0	7.4	4.5	
	10.3	10.0	6.5	
	12.5	12.3	8.0	



BPCA00121280 Series Specification

1 Scope: This specification applies to the Pb Free high current type SMD inductors

2 Part Numbering:



3 Rating:


Operating Temperature: $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$ (Including self - temperature rise)

Storage Temperature(on tape & reel): -20°C to $+40^{\circ}\text{C}$; 75% RH max.

4 Standard Testing Condition:

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

5 Configuration and Dimensions:



A:	12.5 ± 0.4	mm
B:	12.3 ± 0.4	mm
C:	8.0 Max.	mm
D:	4.0 Typ.	mm
E:	6.3 Typ.	mm
F:	3.15 Typ.	mm

Net Weight (grms)

SIZE CODE	Net Weight (grms)
121280	4.1(Typ.)

BPAA00121280 Series Specification

6 Electrical Characteristics:

Part No.	Inductance L(μH)	Percent Tolerance	Test Frequency	Resistance RDC(Ω)	Rated DC Current		Marking
					Isat (A)	Irms (A)	
BPAA001212801R5□A0	1.5	T	100KHz/0.25V	5.5m ±30%	23.50	10.50	1R5
BPAA001212802R2□A0	2.2	T	100KHz/0.25V	6.3m ±30%	20.00	9.70	2R2
BPAA001212803R3□A0	3.3	T	100KHz/0.25V	7.7m ±30%	15.00	9.50	3R3
BPAA001212804R7□A0	4.7	T	100KHz/0.25V	8.7m ±30%	13.00	9.00	4R7
BPAA001212806R8□A0	6.8	T	100KHz/0.25V	10m ±20%	9.70	8.50	6R8
BPAA00121280100□A0	10	M,T	100KHz/0.25V	12m ±20%	9.20	7.70	100
BPAA00121280150□A0	15	M,T	100KHz/0.25V	24m ±20%	7.40	5.10	150
BPAA00121280220□A0	22	M,T	100KHz/0.25V	27m ±20%	5.80	4.50	220
BPAA00121280330□A0	33	M,T	100KHz/0.25V	52m ±20%	4.50	3.60	330
BPAA00121280470□A0	47	M,T	100KHz/0.25V	66m ±20%	4.20	3.20	470
BPAA00121280680□A0	68	M,T	100KHz/0.25V	90m ±20%	3.60	2.70	680
BPAA00121280101□A0	100	M,T	100KHz/0.25V	0.11 ±20%	2.90	2.60	101
BPAA00121280151□A0	150	M,T	100KHz/0.25V	0.17 ±20%	2.40	2.10	151
BPAA00121280221□A0	220	M,T	100KHz/0.25V	0.28 ±20%	1.95	1.60	221
BPAA00121280331□A0	330	M,T	100KHz/0.25V	0.41 ±20%	1.60	1.25	331
BPAA00121280471□A0	470	M,T	100KHz/0.25V	0.59 ±20%	1.30	1.10	471


NOTE: tolerance K = ±10% , M = ±20% , T = ±30%

1. Isat : Based on inductance change ($\Delta L/L_0$: drop 30% Typ.) @ ambient Temperature : 25°C

2. Irms : Based on temperature rise (ΔT : 40°C TYP.)

BPCA00121280 Series Specification

6.1 Construction:



6.2 Material List:


NO.	ITEM	DESCRIPTION & TYPE
1	CORE	FERRITE
2	WIRE	MAGNET WIRE (P180)
3	TERMINAL	Ag/Cu/Ni/Sn

BPCA00121280 Series Specification

ELECTRICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Temperature characteristics	$\Delta L/L_{20^{\circ}\text{C}} \leq \pm 10\%$ $0 \sim 2000 \text{ ppm}/^{\circ}\text{C}$	The test shall be performed after the sample has stabilized in an ambient temperature of -20 to $+85^{\circ}\text{C}$, and the value calculated based on the value applicable in a normal temperature and normal humidity shall be $\Delta L/L_{20^{\circ}\text{C}} \leq \pm 10\%$.

MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Substrate bending	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage or electrical damage.	The sample shall be soldered onto the printed circuit board in figure 1 and a load applied until the figure in the arrow direction is made approximately 3mm. (keep time 30 seconds) PCB dimension shall be the page 7/9 F(Pressurization)  PRESSURE ROD figure-1

BPCA00121280 Series Specification

MECHANICAL

TEST ITEM	SPECIFICATION	
Vibration	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be soldered onto the printed circuit board and when a vibration having an amplitude of 1.52mm and a frequency of from 10 to 55Hz/1 minute repeated should be applied to the 3 directions (X,Y,Z) for 2 hours each. (A total of 6 hours)
Solderability	New solder More than 90%	Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated over the whole of the sample before hard, the sample shall then be preheated for about 2 minutes in a temperature of 130~150°C and after it has been immersed to a depth 0.5mm below for 3±0.2 seconds fully in molten solder M705 with a temperature of 245±5°C. More than 90% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.
Resistance to Soldering heat (reflow soldering)	There shall be no damage or problems.	Temperature profile of reflow soldering The graph shows a temperature profile for reflow soldering. The y-axis is Temperature (°C) with markers at 25, 160, 217, and 260. The x-axis is Time. The profile starts at 25°C, rises through a preheat stage (150-200°C, 60-120 sec), enters a liquidus stage (>217°C, 60-150 sec), reaches a peak soldering temperature of 260°C ± 3°C for 10-30 seconds, and then ramps down at 6°C/sec max. The ramp up is at 3°C/sec max. The specimen shall be passed through the reflow oven with the condition shown in the above profile for 1 time. The specimen shall be stored at standard atmospheric conditions for 1 hour, after which the measurement shall be made.

BPCA00121280 Series Specification

ENVIRONMENT CHARACTERISTICS

TEST ITEM	SPECIFICATION																
High temperature storage	$\Delta L/Lo \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in an atmosphere with a temperature of 125°C and a normal humidity. Upon completion of the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Low temperature storage	$\Delta L/Lo \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in an atmosphere with a temperature of $-40 \pm 3^\circ\text{C}$. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Change of temperature	$\Delta L/Lo \leq \pm 5\%$ There shall be no other damage of problems	The sample shall be subject to 5 continuous cycles, such as shown in the table 2 below and then it shall be subjected to standard atmospheric conditions for 1 hour, after which measurement shall be made. table 2 <table border="1" style="margin: 10px auto; border-collapse: collapse;"> <thead> <tr> <th></th><th>Temperature</th><th>Duration</th></tr> </thead> <tbody> <tr> <td style="text-align: center;">1</td><td style="text-align: center;">$-40 \pm 3^\circ\text{C}$ (Thermostat No.1)</td><td style="text-align: center;">30 min.</td></tr> <tr> <td style="text-align: center;">2</td><td style="text-align: center;">Standard atmospheric</td><td style="text-align: center;">No.1→No.2</td></tr> <tr> <td style="text-align: center;">3</td><td style="text-align: center;">$125 \pm 2^\circ\text{C}$ (Thermostat No.2)</td><td style="text-align: center;">30 min.</td></tr> <tr> <td style="text-align: center;">4</td><td style="text-align: center;">Standard atmospheric</td><td style="text-align: center;">No.2→No.1</td></tr> </tbody> </table>		Temperature	Duration	1	$-40 \pm 3^\circ\text{C}$ (Thermostat No.1)	30 min.	2	Standard atmospheric	No.1→No.2	3	$125 \pm 2^\circ\text{C}$ (Thermostat No.2)	30 min.	4	Standard atmospheric	No.2→No.1
	Temperature	Duration															
1	$-40 \pm 3^\circ\text{C}$ (Thermostat No.1)	30 min.															
2	Standard atmospheric	No.1→No.2															
3	$125 \pm 2^\circ\text{C}$ (Thermostat No.2)	30 min.															
4	Standard atmospheric	No.2→No.1															
Moisture storage	$\Delta L/Lo \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in a temperature of $40 \pm 2^\circ\text{C}$ and a humidity(RH) of 90~95%. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity more than 1 hour.															


Test conditions :

The sample shall be reflow soldered onto the printed circuit board in every test.

BPCA00121280 Series Specification

7 Packaging:


7.1 Packaging -Cover Tape



7.2 Packaging Quantity

TYPE	PCS/REEL
BPCA00121280	400


7.3 Reel Dimensions





BPCA00121280 Series Specification

7 Packaging:

7.4 Tape Dimensions in mm




Unreeling
Direction



8 Recommended Land Pattern:

(STANDARD PATTERN) Unit : mm



BPCA00121280 Series Specification

9 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock or drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components
(refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.