

Power Inductor



BPDR Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

1. Ferrite SMD Shielded Type
2. Various package size and wide inductance range

Applications

1. AP Routers, STBs
2. LCD TVs and monitors
3. Game consoles
4. LED lightings
5. DC/DC converters

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPDR	3.8	3.8	1.6	1 ~ 330
	4.7	4.7	2.0	
	4.7	4.7	3.0	
	5.7	5.7	2.0	
	5.7	5.7	3.0	
	5.7	5.7	5.5	
	6.7	6.7	3.0	
	6.7	6.7	4.0	
	8.0	8.0	3.0	
	8.0	8.0	4.0	
	8.0	8.0	4.5	



BPDR00070740 Series Specification

1 Scope: This specification applies to the Pb Free high current type SMD inductors

2 Part Numbering:



3 Rating:


Operating Temperature range: -40°C ~ +125°C (Including self temp. rise)

Storage Temperature: (on tape & reel): -20°C to +40°C; 75% RH max.

4 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

5 Configuration and Dimensions:



A: 6.70±0.3 mm

B: 6.70±0.3 mm

C: 3.70±0.3 mm

D: 6.50 Typ. mm

E: 6.50 Typ. mm

F: 2.00 Typ. mm

Net Weight (grms)

SIZE CODE	Net Weight (grms)
070740	0.69 (Typ.)

BPDR00070740 Series Specification

6 Electrical Characteristics:

Part No.	Inductance L(μH)	Test Freq.	Resistance RDC(Ω) Max.	Rated DC Current Isat(A) Irms(A)	Tolerance	Marking
BPDR000707401R0□00	1.0	100kHz/0.25V	10m	4.50 4.50	T	1R0
BPDR000707401R5□00	1.5	100kHz/0.25V	11m	4.30 4.30	T	1R5
BPDR000707402R2□00	2.2	100kHz/0.25V	15m	4.00 4.00	T	2R2
BPDR000707403R3□00	3.3	100kHz/0.25V	20m	3.50 3.50	M,T	3R3
BPDR000707403R8□00	3.8	100kHz/0.25V	20m	3.50 3.50	T	3R8
BPDR000707405R0□00	5.0	100kHz/0.25V	24m	2.90 2.90	T	5R0
BPDR000707406R2□00	6.2	100kHz/0.25V	27m	2.50 2.50	T	6R2
BPDR000707406R8□00	6.8	100kHz/0.25V	29m	2.40 2.40	M,T	6R8
BPDR000707407R4□00	7.4	100kHz/0.25V	31m	2.30 2.30	T	7R4
BPDR000707408R2□00	8.2	100kHz/0.25V	34m	2.20 2.20	T	8R2
BPDR000707408R7□00	8.7	100kHz/0.25V	34m	2.20 2.20	T	8R7
BPDR00070740100□00	10	100kHz/0.25V	38m	2.00 2.00	M,T	100
BPDR00070740120□00	12	100kHz/0.25V	53m	1.70 1.70	M,T	120
BPDR00070740150□00	15	100kHz/0.25V	57m	1.60 1.60	M,T	150
BPDR00070740180□00	18	100kHz/0.25V	92m	1.50 1.50	M,T	180
BPDR00070740220□00	22	100kHz/0.25V	96m	1.30 1.30	M,T	220
BPDR00070740270□00	27	100kHz/0.25V	0.109	1.20 1.20	M,T	270
BPDR00070740330□00	33	100kHz/0.25V	0.124	1.10 1.10	M,T	330
BPDR00070740390□00	39	100kHz/0.25V	0.138	1.00 1.00	M,T	390
BPDR00070740470□00	47	100kHz/0.25V	0.155	0.95 0.95	M,T	470
BPDR00070740560□00	56	100kHz/0.25V	0.202	0.85 0.85	M,T	560
BPDR00070740680□00	68	100kHz/0.25V	0.234	0.75 0.75	M,T	680
BPDR00070740820□00	82	100kHz/0.25V	0.324	0.70 0.70	M,T	820
BPDR00070740101□00	100	100kHz/0.25V	0.358	0.65 0.65	K,M,T	101
BPDR00070740221□00	220	100kHz/0.25V	1.50	0.45 0.45	M,T	221
BPDR00070740331□00	330	100kHz/0.25V	1.55	0.35 0.35	M,T	331
BPDR00070740681□00	680	100kHz/0.25V	1.98	0.27 0.27	M,T	681


NOTE: tolerance M=±20% , T=±30%

1.Isat : Based on inductance change ($\Delta L/L_0$: drop 35% Max.) @ambient Temperature : 25℃

2.Irms : Based on temperature rise (ΔT : 40℃ Typ.)

BPDR00070740 Series Specification

6.1 Construction:



6.2 Material List:


NO.	ITEM	DESCRIPTION & TYPE
1	Core	Ferrite
2	Wire	Magnet Wire
3	Terminal	Terminal Copper

BPDR00070740 Series Specification

ELECTRICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Insulation resistance	There shall be no other damage or problems.	DC 100V voltage shall be applied across this sample of top surface and the terminal. The insulation resistance shall be more than $1 \times 10^8 \Omega$.
Dielectric withstand voltage	There shall be no other damage or problems.	AC 100V voltage shall be applied for 1 minute across the top surface and the terminal of this sample
Temperature characteristics	$\Delta L/L20^\circ\text{C} \leq \pm 10\%$ $0 \sim 2000 \text{ ppm}/^\circ\text{C}$	The test shall be performed after the sample has stabilized in an ambient temperature of -20 to $+85^\circ\text{C}$, and the value calculated based on the value applicable in a normal temperature and normal humidity shall be $\Delta L/L20^\circ\text{C} \leq \pm 10\%$.

MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Substrate bending	$\Delta L/L_0 \leq \pm 10\%$ There shall be no mechanical damage or electrical damage.	The sample shall be soldered onto the printed circuit board in figure 1 and a load applied until the figure in the arrow direction is made approximately 3mm. (keep time 30 seconds) PCB dimension shall be the page 7/9 F(Pressurization)  PRESSURE ROD figure-1

BPDR00070740 Series Specification

MECHANICAL

TEST ITEM	SPECIFICATION	
Vibration	$\Delta L/L_0 \leq \pm 10\%$ There shall be no mechanical damage.	The sample shall be soldered onto the printed circuit board and when a vibration having an amplitude of 1.52mm and a frequency of from 10 to 55Hz/1 minute repeated should be applied to the 3 directions (X,Y,Z) for 2 hours each. (A total of 6 hours)
Solderability	New solder More than 90%	Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated over the whole of the sample before hard, the sample shall then be preheated for about 2 minutes in a temperature of 130~150°C and after it has been immersed to a depth 0.5mm below for 3±0.2 seconds fully in molten solder M705 with a temperature of 245±5°C. More than 90% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.
Resistance to Soldering heat (reflow soldering)	There shall be no damage or problems.	Temperature profile of reflow soldering The specimen shall be passed through the reflow oven with the condition shown in the above profile for 1 time. The specimen shall be stored at standard atmospheric conditions for 1 hour, after which the measurement shall be made.

BPDR00070740 Series Specification


ENVIRONMENT CHARACTERISTICS

TEST ITEM	SPECIFICATION																
High temperature storage	$\Delta L/Lo \leq \pm 10\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in an atmosphere with a temperature of 125°C and a normal humidity. Upon completion of the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Low temperature storage	$\Delta L/Lo \leq \pm 10\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in an atmosphere with a temperature of $-40 \pm 2^\circ\text{C}$. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Change of temperature	$\Delta L/Lo \leq \pm 10\%$ There shall be no other damage of problems	The sample shall be subject to 5 continuous cycles, such as shown in the table 2 below and then it shall be subjected to standard atmospheric conditions for 1 hour, after which measurement shall be made. table 2 <table border="1"> <thead> <tr> <th></th><th>Temperature</th><th>Duration</th></tr> </thead> <tbody> <tr> <td>1</td><td>$-40 \pm 2^\circ\text{C}$ (Thermostat No.1)</td><td>30 min.</td></tr> <tr> <td>2</td><td>Standard atmospheric</td><td>No.1→No.2</td></tr> <tr> <td>3</td><td>125°C (Thermostat No.2)</td><td>30 min.</td></tr> <tr> <td>4</td><td>Standard atmospheric</td><td>No.2→No.1</td></tr> </tbody> </table>		Temperature	Duration	1	$-40 \pm 2^\circ\text{C}$ (Thermostat No.1)	30 min.	2	Standard atmospheric	No.1→No.2	3	125°C (Thermostat No.2)	30 min.	4	Standard atmospheric	No.2→No.1
	Temperature	Duration															
1	$-40 \pm 2^\circ\text{C}$ (Thermostat No.1)	30 min.															
2	Standard atmospheric	No.1→No.2															
3	125°C (Thermostat No.2)	30 min.															
4	Standard atmospheric	No.2→No.1															
Moisture storage	$\Delta L/Lo \leq \pm 10\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in a temperature of $40 \pm 2^\circ\text{C}$ and a humidity(RH) of $90 \sim 95\%$. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity more than 1 hour.															
Test conditions : The sample shall be reflow soldered onto the printed circuit board in every test.																	

BPDR00070740 Series Specification

7 Packaging:

7.1 Packaging -Cover Tape




7.2 Packaging Quantity


TYPE	PCS/REEL
BPDR00070740	1000

7.3 Reel Dimensions

Unit : mm



7.4 Tape Dimensions in mm



BPDR00070740 Series Specification

9 Note:


1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock or drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.

BPDR00070740 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

@100kHz/0.25V



TEMPERATURE vs. DC CURRENT

