

Power Inductor



BPSA Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

- 1. Ferrite SMD Shielded Type
- 2. Low DCR

Applications

- 1. TV, Laptop
- 2. Mainboard
- 3. Commercial devices

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPSA	6.3	6.3	3.0	1.5 ~ 1500
	7.3	7.3	4.8	
	7.3	7.3	5.8	
	12.5	12.5	5.8	



BPSA00060630 Series Specification

1 Scope: This specification applies to SMD Shielded Power Inductors

2 Part Numbering:




3 Rating:

Operating Temperature: - 40°C ~ + 125°C (Including self temp. rise)

Storage Temperature: - 40°C ~ + 125°C (For after the circuit board is mounted)

Storage Temperature: (on tape & reel): -20°C to +40°C; 75% RH max.

4 Marking:



Ex Marking : 221


Marking color : Black

5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

BPSA00060630 Series Specification

6 Configuration and Dimensions and Unit Weight:



Dimensions in mm

TYPE	060630
A	6.3 Max.
B	6.3 Max.
C	3.0 Max.
D	2.0
E	4.0
F	0.9

Net Weight (grms)

SIZE CODE	Net Weight (grms)
060630	0.37(Typ.)

7 Electrical Characteristics:

Part No.	Inductance (μ H)	Test Freq.	SRF (MHz)Min.	RDC (m Ω)Max.	Isat (A)	Irms (A)	Tolerance ($\pm$ %)	Marking
BPSA000606306R8M00	6.8	100 kHz, 1V	35	42	1.5	2.2	20	6R8
BPSA00060630100M00	10	100 kHz, 1V	20	63.8	1.3	1.8	20	100
BPSA00060630150M00	15	100 kHz, 1V	15	89.4	1	1.4	20	150
BPSA00060630220M00	22	100 kHz, 1V	10	124	0.77	1.3	20	220
BPSA00060630330M00	33	100 kHz, 1V	7	177	0.69	1.1	20	330
BPSA00060630470M00	47	100 kHz, 1V	5	252	0.59	0.92	20	470
BPSA00060630680M00	68	100 kHz, 1V	4	348	0.5	0.78	20	680
BPSA00060630101M00	100	100 kHz, 1V	4	516	0.42	0.64	20	101
BPSA00060630151M00	150	100 kHz, 1V	4	780	0.34	0.5	20	151
BPSA00060630221M00	220	100 kHz, 1V	3.2	1170	0.26	0.38	20	221

NOTE: □-tolerance M=±20%

1. Operating temperature range - 4 0 °C ~ 1 2 5 °C(Including self - temperature rise)


2. Isat for Inductance drop 30% from its value without current.

3. Irms for a 25°C temperature rise from 25°C ambient.

BPSA00060630 Series Specification

8 BPSA00060630 Series

8.1 Construction:



8.2 Material List:

No	Part	Material
1	Core	Ferrite
2	Wire	Magnet Wire
3	Terminal	Terminal Copper

BPSA00060630 Series Specification

9 Reliability Of Ferrite Wire Wound Power Inductor

1-1.Mechanical Performance


No	Item	Specification	Test Method
1-1-1	Vibration	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-2	Resistance to Soldering Heat	Appearance: No damage	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260 ± 5 °C Immersion Time: 10 ± 1 sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 245 ± 5 °C Immersion Time: 4 ± 1 sec
1-1-4	Resistance to solvent	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.

1-2.Environmental Performance

No	Item	Specification	Test Method															
1-2-1	Temperature Shock	Appearance: No damage Inductance:within±10% of initial value	10 cycles (Air to Air) 1 cycles shall consist of: 30 minutes exposure to −55 ℃ 30 minutes exposure to 125 ℃ 15 seconds maximum transition between temperatures															
1-2-2	Temperature Cycle		One cycle: <table><tr><th>Step</th><th>Temperature (℃)</th><th>Time (min)</th></tr><tr><td>1</td><td>-40±3</td><td>30</td></tr><tr><td>2</td><td>25±2</td><td>3</td></tr><tr><td>3</td><td>125±3</td><td>30</td></tr><tr><td>4</td><td>25±2</td><td>3</td></tr></table>	Step	Temperature (℃)	Time (min)	1	-40±3	30	2	25±2	3	3	125±3	30	4	25±2	3
Step	Temperature (℃)		Time (min)															
1	-40±3		30															
2	25±2		3															
3	125±3	30																
4	25±2	3																
1-2-3	Humidity Resistance	Total: 100cycles Measured after exposure in the room condition for 24hrs																
1-2-4	Heat Life	Temperature: 40±2℃ Relative Humidity: 90 ~ 95% Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-5	Cold Resistance	Temperature: 85±3℃ Applied Current: Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs																
		Temperature: -40±3℃ Time: 1000hrs Measured after exposure in the room condition for 24hrs																

BPSA00060630 Series Specification

Reflow Soldering Profile



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C


管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	—	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	—
實際時間 Time result	—	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	—

BPSA00060630 Series Specification

11 Packaging:

11.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



11.2 Packaging Quantity

TYPE	PCS/REEL
060630	1000

11.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
060630	330	100	13	16


BPSA00060630 Series Specification

11 Packaging:

11.4 Tape Dimensions in mm



12 Recommended Land Pattern:





13 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.



BPSA00060630 Series Specification

14 Graph:



BPSA000606306R8M00





BPSA00060630100M00



BPSA00060630150M00





BPSA00060630220M00





BPSA00060630 Series Specification

14 Graph:



BPSA00060630330M00





BPSA00060630470M00



BPSA00060630680M00





BPSA00060630101M00



BPSA00060630 Series Specification

14 Graph:

BPSA00060630151M00



BPSA00060630221M00

