

Power Inductor



BMRA Series



Overview

BMRx series is designed for low profile type with low RDC and ultra large current.

Its molded magnetic shielded type is suitable for high-density mounting and ultra low buzz noise.

Soldering conditions can be easily confirmed when mounting onto the board.

This series also provides customers with embossed carrier type packaging for automatic mounting machine.

Benefits

1. High rated current
2. Ultra low buzz noise

Applications

1. DC-DC converters
2. Switchs and servers
3. DC-DC converters, inverters, and battery management systems.
4. Base stations, 5G infrastructure
5. Consumer Electronics: Smartphones, laptops, tablets, wearable devices, and gaming consoles.

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BMRA	4.1	4.6	1.2	0.1 ~ 33
	4.1	4.6	1.5	
	4.1	4.6	2.0	
	5.2	5.4	1.2	
	5.4	5.7	1.5	
	5.4	5.7	1.8	
	5.4	5.7	3.0	
	6.6	7.3	1.3	
	6.6	7.3	3.0	



BMRA00060630 Series Specification

1 Scope This specification applies to large current and low loss SMD power inductor.

2 Part numbering




3 Temperature rating

Operating Temperature: -55°C to 125°C.

Storage Temperature: (on tape & reel): -20°C to +40°C; 75% RH max.

4 Marking




Marking : 1R0

5 Standard testing condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

BMRA00060630 Series Specification

6 Configuration and dimensions



Dimensions in mm

Type	060630
A	6.6 ± 0.2
B	6.95 ± 0.35
C	3.0 Max
D	3.0 ± 0.3
F	1.6 ± 0.5

Size Code	Net weight(grms)
060630	0.72(typ.)

7 Electrical characteristics


Part number	Inductance (uH)	Tolerance (±%)	Test Freq.	Irms (A) Typ.	Isat (A) Typ.	RDC (mΩ) Max.(Typ.)	Marking
BMRA00060630R10MA1	0.1	20	100kHz,0.5V	37	45	1.5(1.3)	R10
BMRA00060630R22MA1	0.22	20	100kHz,0.5V	23	40	2.8(2.5)	R22
BMRA00060630R33MA1	0.33	20	100kHz,0.5V	20	33	4.2(4)	R33
BMRA00060630R47MA1	0.47	20	100kHz,0.5V	16.5	27	5.5(5)	R47
BMRA00060630R56MA1	0.56	20	100kHz,0.5V	16.5	27	5.5(5)	R56
BMRA00060630R68MA1	0.68	20	100kHz,0.5V	15	24	6.3(5.7)	R68
BMRA00060630R82MA1	0.82	20	100kHz,0.5V	13	23	8(7.5)	R82
BMRA00060630R1R0MA1	1	20	100kHz,0.5V	12	22	10(9)	1R0
BMRA00060630R1R5MA1	1.5	20	100kHz,0.5V	9.5	18	15(13.5)	1R5
BMRA00060630R1R8MA1	1.8	20	100kHz,0.5V	9.5	14	15(13.5)	1R8
BMRA00060630R2R2MA1	2.2	20	100kHz,0.5V	8.5	14	20(17)	2R2
BMRA00060630R3R3MA1	3.3	20	100kHz,0.5V	6	12	35(32)	3R3
BMRA00060630R4R7MA1	4.7	20	100kHz,0.5V	5.5	9	40(35)	4R7
BMRA00060630R5R6MA1	5.6	20	100kHz,0.5V	5.5	8	40(35)	5R6
BMRA00060630R6R8MA1	6.8	20	100kHz,0.5V	4.5	8	60(54)	6R8
BMRA00060630R150MA1	15	20	100kHz,0.5V	3	5	122(111)	150
BMRA00060630R220MA1	22	20	100kHz,0.5V	3	3.2	145(130)	220
BMRA00060630R330MA1	33	20	100kHz,0.5V	2	3	270(245)	330

Note:

- Operating temperature range -55°C to 125°C.
- Isat for Inductance drop 30% from its value without current.
- Irms for a 40°C temperature rise from 25°C ambient.
- The part temperature (ambient + temp rise) should not exceed 125°C under worst case operating conditions.
Circuit design 125°C under worst case operating conditions. Component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- Absolute maximum voltage 30V DC. (Based on test method, it may not the same under different application, it is recommended to verify first.)

BMRA00060630 Series Specification

8 BMRA00060630 Series 8.1 Construction



8.2 Material List

Item	Part	Description
1	Magnetic core	Magnetic metal powder
2	Coil	Enameled copper wire
3	Terminals	Copper based terminal

BMRA00060630 Series Specification

9 Reliability test items

1-1.Mechanical Performance


No	Item	Specification	Test Method
1-1-1	Vibration	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-2	Resistance to Soldering Heat	Appearance: No damage	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260 ± 5 °C Immersion Time: 10 ± 1 sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 245 ± 5 °C Immersion Time: 4 ± 1 sec
1-1-4	Resistance to solvent	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.

1-2.Environmental Performance

No	Item	Specification	Test Method															
1-2-1	Temperature Shock	Appearance: No damage Inductance:within±10% of initial value	10 cycles (Air to Air) 1 cycles shall consist of: 30 minutes exposure to -55℃ 30 minutes exposure to 125℃ 15 seconds maximum transition between temperatures															
1-2-2	Temperature Cycle		One cycle: <table><tr><th>Step</th><th>Temperature (℃)</th><th>Time (min)</th></tr><tr><td>1</td><td>-55±3</td><td>30</td></tr><tr><td>2</td><td>25±2</td><td>3</td></tr><tr><td>3</td><td>125±3</td><td>30</td></tr><tr><td>4</td><td>25±2</td><td>3</td></tr></table>	Step	Temperature (℃)	Time (min)	1	-55±3	30	2	25±2	3	3	125±3	30	4	25±2	3
Step	Temperature (℃)		Time (min)															
1	-55±3		30															
2	25±2		3															
3	125±3	30																
4	25±2	3																
1-2-3	Humidity Resistance	Total: 100cycles Measured after exposure in the room condition for 24hrs																
1-2-4	Heat Life	Temperature: 40±2℃ Relative Humidity: 90 ~ 95% Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-5	Cold Resistance	Temperature: 85±3℃ Relative Humidity: 20% Applied Current: Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs																
		Temperature: -55±3℃ Relative Humidity: 0% Time: 1000hrs Measured after exposure in the room condition for 24hrs																

BMRA00060630 Series Specification

10 Recommended IR reflow profile



Lead-Free(LF)

Refer to J-STD-020F

Item	Ramp-up	Pre-heating	Reflow	Peak Temp.	Cooling
Temp. scope	R.T. ~150 °C	150 °C~200 °C	217 °C	260±5 °C	Peak Temp. 150 °C
Time spec	-	60~120 sec	60~150 sec	20~40 sec	-

Note:


1. IR reflow times: within 3 times.
2. Nitrogen adopted is recommended while in IR reflow.

BMRA00060630 Series Specification

11 Packaging

11.1 Packaging-cover tape


The force for tearing off cover tape is 10 to 130 grams.



11.2 Packaging quantity

Type	pcs/reel
060630	1000

11.3 Reel dimensions




Dimensions in mm

Type	A	B	C	D
060630	330	100	13	16

BMRA00060630 Series Specification


11 Packaging

11.4 Tape dimensions in mm



Type	A_0	B_0	K_0	D	E	W	P	P_0	P_2
060630	6.9	7.6	3.4	1.5	1.75	16	12	4	2

12 Recommended pattern



Dimensions in mm







Type	A	B	C
060630	3.5	3.7	8.4

13 Note

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Don't design/ mount any components in contact with this product.
3. The moisture sensitivity level (MSL) of products is classified as level 1.
4. Shelf life: 1 years from the date of shipment.







BMRA00060630 Series Specification

14 Graph



BMRA00060630 Series Specification

14 Graph



BMRA00060630 Series Specification

14 Graph

