Metal Surface Mount WiFi Antenna

TWA422CC01 – 2.4 to 2.5 GHz/5.15 to 5.85GHz

OBSOLETE



Features & Applications:

- *WiFi antenna is designed for use on metal surface*
- *FPCB with adhesive*
- *Size 29x26.4x2.45mm*
- *1.13mm cable with I-PEX MHF 4L*
- *RoHS Compliant*

ELECTRICAL SPECIFICATIONS @ 25°C				
General Specifications				
Antenna type	**Nominal Impedance**	**Polarization**	**Radiation pattern**	**Power withstanding**
PIFA	50Ω	Linear	Omni	1W

Frequency (MHz)	2400-2500	5150-5850
Return Loss(dB)	<-7	<-9
Peak Gain (dBi)	1.75	5.72
Efficiency (%)	36	50


MECHANICAL SPECIFICATIONS						
TWA422CC01						
Dimension (Length x Width x Height)	**Material**	**Color**	**Cable Type**	**Connector Type**	**Cable length**	**Weight**
29mm x 26.4mm x 2.45mm	FPCB	Black	1.13 coaxial cable	I-PEX MHF 4L	95mm	1.97g

ENVIRONMENTAL SPECIFICATIONS			
TWA422CC01			
Storage Temperature	**Operating Temperature**	**Ingress Protection**	**RoHS Compliant**
-40/+85° C	-40/+85° C	N/A	Yes

OBSOLETE

Mechanical Drawing

TWA422CC01



Units: mm


OBSOLETE

Test Setup

General / Chamber Setup

- Measured at Pulse YP (ETS Lindgren Chamber)
- Test data measured with 95mm cable
- The antenna is mounted on a 100mm x 100mm x 1mm metal plate


Measurement setup




OBSOLETE

Charts – VSWR

Test data




Antenna assembled centered on a 100 mm x 100 mm x 1 mm metal plate




* Data measured with a 100mm x 100mm x 1mm metal plate

Charts –Return Loss

Test data




Antenna assembled centered on a 100 mm x 100 mm x 1 mm metal plate




* Data measured with a 100mm x 100mm x 1mm metal plate

Charts – Peak Gain(dBi)

Test data




Antenna assembled centered on a 100 mm x 100 mm x 1 mm metal plate




* Data measured with a 100mm x 100mm x 1mm metal plate

Charts – Efficiency(dB)

Test data



Antenna assembled centered on a 100 mm x 100 mm x 1 mm metal plate





* Data measured with a 100mm x 100mm x 1mm metal plate


OBSOLETE

Radiation Pattern – XY Gain Plots

Test data










OBSOLETE

Radiation Pattern – ZX Gain Plots

Test data










OBSOLETE

Radiation Pattern – YZ Gain Plots

Test data







OBSOLETE

PACKAGING

TWA422CC01

10 PCS/PE bag
10 PE bag/foam bag
50 foam bag/carton box
Total 5000 PCS/carton box
Package box: 460mm*235mm*140mm



Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2020. Pulse Electronics, Inc. All rights reserved.
Company address: Pulse Electronics, a YAGEO Company, 15255 Innovation Drive, Suite #100, San Diego, CA 92128
'YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.'