

## Overview


Dual in-line (DIL) metallized polyester (PET) film capacitor for surface mounting is encapsulated in a self-extinguishing material, meeting the requirements of UL 94 V-0.

## Applications

Typical applications include high frequency switched-mode power supplies, DC/DC converters and input/output filtering.

## Benefits

- Rated voltage: 50 – 630 VDC
- Rated voltage: 30 – 220 VAC
- Capacitance range: 0.033 – 15  $\mu$ F
- Capacitance tolerance:  $\pm 5\%$ ,  $\pm 10\%$ , other tolerances on request
- Climatic category: 55/125/56
- RoHS compliant and lead-free terminations
- Operating temperature range of  $-55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$



## Customer Part Number

| MDC                                | 10                | 333                                                                                                                                                 | K                                                               | 50                             | A52                 | P3                                                                           | TUBE                       |
|------------------------------------|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|--------------------------------|---------------------|------------------------------------------------------------------------------|----------------------------|
| Series                             | Lead Spacing (mm) | Capacitance Code (pF)                                                                                                                               | Capacitance Tolerance                                           | Rated Voltage (VDC)            | Size Code           | Number of Leads per Side                                                     | Packaging                  |
| Dual In-Line, Metallized Polyester | 10<br>15          | First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>Other tolerances on request. | 50<br>100<br>250<br>400<br>630 | See Dimension Table | P3 = 3 leads<br>P4 = 4 leads<br>P5 = 5 leads<br>P7 = 7 leads<br>P8 = 8 leads | See Ordering Options Table |

## KEMET Internal Part Number

| F               | 15                                 | 3                                                                       | A                 | A                     | 333                                                                                                                                                 | K                                                              | 050                                                          | T                          |
|-----------------|------------------------------------|-------------------------------------------------------------------------|-------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|--------------------------------------------------------------|----------------------------|
| Capacitor Class | Series                             | Number of Leads per Side                                                | Lead Spacing (mm) | Size Code             | Capacitance Code (pF)                                                                                                                               | Capacitance Tolerance                                          | Rated Voltage (VDC)                                          | Packaging                  |
| F = Film        | Dual In-line, Metallized Polyester | 3 = 3 leads<br>4 = 4 leads<br>5 = 5 leads<br>7 = 7 leads<br>8 = 8 leads | A = 10<br>B = 15  | A = Standard box size | First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>Other tolerances on request | 050 = 50<br>100 = 100<br>250 = 250<br>400 = 400<br>630 = 630 | See Ordering Options Table |



# Surface Mount Polyester (PET) Film Capacitor

## MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

### Ordering Options Table

| Packaging Type             |                             | KEMET Packaging Code | Legacy Packaging Code |
|----------------------------|-----------------------------|----------------------|-----------------------|
| Standard Packaging Options |                             |                      |                       |
| Bulk (Tube)                |                             | T                    | TUBE                  |
| Case Size A53              | Tape & Reel (Standard Reel) | VV687                | TR32                  |

### Dimensions – Millimeters



| Legacy Size Code | Leads per Side | P1   | P2   | P3 <sup>(1)</sup> | B    | H    | L     | H1   | L2   | L3 <sup>(2)</sup> | W     | X     | Y    | Z       | LL   | G   |
|------------------|----------------|------|------|-------------------|------|------|-------|------|------|-------------------|-------|-------|------|---------|------|-----|
|                  |                | ±0.2 | ±0.2 | ±0.2              | ±0.2 | ±0.2 | ±0.2  | ±0.4 | ±0.2 | Maximum           | ±0.05 | ±0.05 | ±0.2 | Nominal | ±0.2 | Max |
| A52              | 3              | 10.0 | 2.54 | 5.08              | 12.2 | 5.75 | 11.0  | 7.75 | 2.96 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A53              | 3              | 10.0 | 2.54 | 5.08              | 12.7 | 8.5  | 14.0  | 10.5 | 4.46 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |
| A54              | 3              | 10.0 | 2.54 | 5.08              | 12.2 | 5.75 | 13.5  | 7.75 | 4.21 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A55              | 3              | 10.0 | 2.54 | 5.08              | 12.2 | 5.75 | 16.5  | 7.75 | 5.71 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| B53              | 3              | 15.0 | 2.54 | 5.08              | 16.5 | 5.75 | 11.0  | 7.75 | 2.96 | 0.2               | 0.5   | 0.35  | 1.5  | 0.6     | 2.2  | 0.3 |
| B55              | 3              | 15.0 | 2.54 | 5.08              | 16.5 | 5.75 | 12.2  | 7.75 | 3.56 | 0.2               | 0.5   | 0.35  | 1.5  | 0.6     | 2.2  | 0.3 |
| A53              | 4              | 10.0 | 2.54 | 7.62              | 12.7 | 8.5  | 14.0  | 10.5 | 3.19 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |
| A54              | 4              | 10.0 | 2.54 | 7.62              | 12.2 | 5.75 | 13.5  | 7.75 | 2.94 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A55              | 4              | 10.0 | 2.54 | 7.62              | 12.2 | 5.75 | 16.5  | 7.75 | 4.44 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| B55              | 4              | 15.0 | 2.54 | 7.62              | 16.5 | 5.75 | 12.2  | 7.75 | 2.29 | 0.2               | 0.5   | 0.35  | 1.5  | 0.6     | 2.2  | 0.3 |
| A55              | 5              | 10.0 | 2.54 | 10.16             | 12.2 | 5.75 | 16.5  | 7.75 | 3.17 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A58              | 7              | 10.0 | 2.54 | 15.24             | 12.7 | 10.5 | 23.0  | 12.5 | 3.88 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |
| A58              | 8              | 10.0 | 2.54 | 17.78             | 12.7 | 10.5 | 23.00 | 12.5 | 2.61 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |




(1) P3 represents the cumulative tolerance of all leads.

(2) L3 represents the extent to which the center line of the leads misaligns with the center line of the body. Dimension shown is the maximum such misalignment allowed.

# Surface Mount Polyester (PET) Film Capacitor

## MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

### Dimensions – Millimeters cont.



| Legacy Size Code | Leads per Side | P1   | P2   | P3 <sup>(1)</sup> | B    | H    | L     | H1   | L2   | L3 <sup>(2)</sup> | W     | X     | Y    | Z       | LL   | G   |
|------------------|----------------|------|------|-------------------|------|------|-------|------|------|-------------------|-------|-------|------|---------|------|-----|
|                  |                | ±0.2 | ±0.2 | ±0.2              | ±0.2 | ±0.2 | ±0.2  | ±0.4 | ±0.2 | Maximum           | ±0.05 | ±0.05 | ±0.2 | Nominal | ±0.2 | Max |
| A52              | 3              | 10.0 | 2.54 | 5.08              | 12.2 | 5.75 | 11.0  | 7.75 | 2.96 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A53              | 3              | 10.0 | 2.54 | 5.08              | 12.7 | 8.5  | 14.0  | 10.5 | 4.46 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |
| A54              | 3              | 10.0 | 2.54 | 5.08              | 12.2 | 5.75 | 13.5  | 7.75 | 4.21 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A55              | 3              | 10.0 | 2.54 | 5.08              | 12.2 | 5.75 | 16.5  | 7.75 | 5.71 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| B53              | 3              | 15.0 | 2.54 | 5.08              | 16.5 | 5.75 | 11.0  | 7.75 | 2.96 | 0.2               | 0.5   | 0.35  | 1.5  | 0.6     | 2.2  | 0.3 |
| B55              | 3              | 15.0 | 2.54 | 5.08              | 16.5 | 5.75 | 12.2  | 7.75 | 3.56 | 0.2               | 0.5   | 0.35  | 1.5  | 0.6     | 2.2  | 0.3 |
| A53              | 4              | 10.0 | 2.54 | 7.62              | 12.7 | 8.5  | 14.0  | 10.5 | 3.19 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |
| A54              | 4              | 10.0 | 2.54 | 7.62              | 12.2 | 5.75 | 13.5  | 7.75 | 2.94 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A55              | 4              | 10.0 | 2.54 | 7.62              | 12.2 | 5.75 | 16.5  | 7.75 | 4.44 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| B55              | 4              | 15.0 | 2.54 | 7.62              | 16.5 | 5.75 | 12.2  | 7.75 | 2.29 | 0.2               | 0.5   | 0.35  | 1.5  | 0.6     | 2.2  | 0.3 |
| A55              | 5              | 10.0 | 2.54 | 10.16             | 12.2 | 5.75 | 16.5  | 7.75 | 3.17 | 0.2               | 0.5   | 0.35  | 1.5  | 0.25    | 2.2  | 0.3 |
| A58              | 7              | 10.0 | 2.54 | 15.24             | 12.7 | 10.5 | 23.0  | 12.5 | 3.88 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |
| A58              | 8              | 10.0 | 2.54 | 17.78             | 12.7 | 10.5 | 23.00 | 12.5 | 2.61 | 0.2               | 0.5   | 0.35  | 1.5  | 0       | 2.0  | 0.5 |

(1) P3 represents the cumulative tolerance of all leads.

(2) L3 represents the extent to which the center line of the leads misaligns with the center line of the body. Dimension shown is the maximum such misalignment allowed.

Surface Mount Polyester (PET) Film Capacitor  
MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

Performance Characteristics

|                            |                                                                        |             |                  |                 |              |
|----------------------------|------------------------------------------------------------------------|-------------|------------------|-----------------|--------------|
| Rated Voltage (VDC)        | 50                                                                     | 100         | 250              | 400             | 630          |
| Rated Voltage (VAC)        | 30                                                                     | 63          | 160              | 200             | 220          |
| Capacitance Range (μF)     | 0.033 – 15                                                             | 0.033 – 10  | 0.033 – 1.5      | 0.033 – 0.47    | 0.033 – 0.18 |
| Capacitance Tolerance      | ±5%, ±10%, other tolerances on request                                 |             |                  |                 |              |
| Category Temperature Range | -55°C to +125°C                                                        |             |                  |                 |              |
| Rated Temperature          | +85°C                                                                  |             |                  |                 |              |
| Voltage Derating           | The rated voltage should be decreased by 1.25%/°C from +85°C to +125°C |             |                  |                 |              |
| Climatic Category          | 55/125/56                                                              |             |                  |                 |              |
| Test Voltage               | 1.6 x V <sub>R</sub> , 60 seconds                                      |             |                  |                 |              |
| Insulation Resistance      | Measured at +20°C According to IEC 60384-2                             |             |                  |                 |              |
|                            | Minimum Value Between Terminals                                        |             |                  |                 |              |
|                            |                                                                        | C ≤ 0.33 μF |                  | C > 0.33 μF     |              |
|                            | V <sub>R</sub> ≤ 100                                                   | 15,000 MΩ   |                  | 5,000 MΩ • μF   |              |
|                            | V <sub>R</sub> > 100                                                   | 30,000 MΩ   |                  | 10,000 MΩ • μF  |              |
| Dissipation Factor         | Maximum Values at +23°C                                                |             |                  |                 |              |
|                            |                                                                        | C ≤ 0.1 μF  | 0.1 < C < 3.3 μF | 3.3 ≤ C ≤ 10 μF | C > 10 μF    |
|                            | 1 kHz                                                                  | 0.8%        | 0.8%             | 0.8%            | 0.8%         |
|                            | 10 kHz                                                                 | 1.5%        | 1.5%             | 1.5%            | 2.0%         |
|                            | 100 kHz                                                                | 2.5%        | 5.0%             |                 |              |
| Self Inductance            | Approximately 4 nH                                                     |             |                  |                 |              |


Environmental Compliance

All KEMET surface mount capacitors are RoHS compliant.




Surface Mount Polyester (PET) Film Capacitor  
MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

ESR vs. Frequency



Impedance vs. Frequency



Maximum  $V_{rms}$  (V) vs. Frequency

| Value  | Rated Voltage | Case Size | 1 kHz | 10 kHz | 100 kHz | 500 kHz | 1 MHz |
|--------|---------------|-----------|-------|--------|---------|---------|-------|
| 1.0 μF | 250 V         | A57       | 150.0 | 36.0   | 9.2     | 2.9     | 1.3   |
| 2.2 μF | 100 V         | A52       | 50.0  | 25.0   | 5.0     | 1.2     | 0.6   |
| 3.9 μF | 100 V         | A52       | 50.0  | 18.0   | 4.0     | 1.0     | 0.3   |
| 4.7 μF | 100 V         | A54       | 50.0  | 16.0   | 3.5     | 0.7     | 0.2   |
| 6.8 μF | 100 V         | A57       | 50.0  | 15.5   | 2.2     | 0.5     | 0.2   |
| 10 μF  | 100 V         | A58       | 50.0  | 15.0   | 2.0     | 0.4     | 0.2   |

Maximum  $I_{rms}$  (V) vs. Frequency

| Value  | Rated Voltage | Case Size | 1 kHz | 10 kHz | 100 kHz | 500 kHz | 1 MHz |
|--------|---------------|-----------|-------|--------|---------|---------|-------|
| 1.0 μF | 250 V         | A57       | 1.0   | 2.2    | 5.5     | 9.0     | 10.0  |
| 2.2 μF | 100 V         | A52       | 1.5   | 2.3    | 6.0     | 7.5     | 10.0  |
| 3.9 μF | 100 V         | A52       | 2.0   | 4.0    | 10.0    | 11.0    | 11.5  |
| 4.7 μF | 100 V         | A54       | 2.0   | 4.5    | 10.0    | 12.5    | 12.5  |
| 6.8 μF | 100 V         | A57       | 3.0   | 6.0    | 11.0    | 13.0    | 13.5  |
| 10 μF  | 100 V         | A58       | 4.0   | 9.0    | 13.0    | 14.0    | 14.5  |

Surface Mount Polyester (PET) Film Capacitor  
MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

Table 1 – Ratings & Part Number Reference

| VDC | VAC | Cap Value (µF) | Size Code (New/ Legacy) | Dimensions in mm |        |        | Lead Spacing (p) | ESR 500 kHz (mΩ) | New KEMET Part Number | Legacy Part Number       |
|-----|-----|----------------|-------------------------|------------------|--------|--------|------------------|------------------|-----------------------|--------------------------|
|     |     |                |                         | B                | H      | L      |                  |                  |                       |                          |
| 50  | 30  | 0.033          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 390              | F153AA333(1)050T      | MDC10333(1)50A52P3TUBE   |
| 50  | 30  | 0.039          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 330              | F153AA393(1)050T      | MDC10393(1)50A52P3TUBE   |
| 50  | 30  | 0.047          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 270              | F153AA473(1)050T      | MDC10473(1)50A52P3TUBE   |
| 50  | 30  | 0.056          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 230              | F153AA563(1)050T      | MDC10563(1)50A52P3TUBE   |
| 50  | 30  | 0.068          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 190              | F153AA683(1)050T      | MDC10683(1)50A52P3TUBE   |
| 50  | 30  | 0.082          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 160              | F153AA823(1)050T      | MDC10823(1)50A52P3TUBE   |
| 50  | 30  | 0.10           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 130              | F153AA104(1)050T      | MDC10104(1)50A52P3TUBE   |
| 50  | 30  | 0.12           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 110              | F153AA124(1)050T      | MDC10124(1)50A52P3TUBE   |
| 50  | 30  | 0.15           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 85               | F153AA154(1)050T      | MDC10154(1)50A52P3TUBE   |
| 50  | 30  | 0.18           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 70               | F153AA184(1)050T      | MDC10184(1)50A52P3TUBE   |
| 50  | 30  | 0.22           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 58               | F153AA224(1)050T      | MDC10224(1)50A52P3TUBE   |
| 50  | 30  | 0.27           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 47               | F153AA274(1)050T      | MDC10274(1)50A52P3TUBE   |
| 50  | 30  | 0.33           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 39               | F153AA334(1)050T      | MDC10334(1)50A52P3TUBE   |
| 50  | 30  | 0.39           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 33               | F153AA394(1)050T      | MDC10394(1)50A52P3TUBE   |
| 50  | 30  | 0.47           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 30               | F153AA474(1)050T      | MDC10474(1)50A52P3TUBE   |
| 50  | 30  | 0.56           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 26               | F153AA564(1)050T      | MDC10564(1)50A52P3TUBE   |
| 50  | 30  | 0.68           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 21               | F153AA684(1)050T      | MDC10684(1)50A52P3TUBE   |
| 50  | 30  | 0.82           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 18               | F153AA824(1)050T      | MDC10824(1)50A52P3TUBE   |
| 50  | 30  | 1.0            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 15               | F153AA105(1)050T      | MDC10105(1)50A52P3TUBE   |
| 50  | 30  | 1.2            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 14               | F153AA125(1)050T      | MDC10125(1)50A52P3TUBE   |
| 50  | 30  | 1.5            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 13               | F153AA155(1)050T      | MDC10155(1)50A52P3TUBE   |
| 50  | 30  | 1.8            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 12               | F153AA185(1)050T      | MDC10185(1)50A52P3TUBE   |
| 50  | 30  | 2.2            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 11               | F153AA225(1)050T      | MDC10225(1)50A52P3TUBE   |
| 50  | 30  | 2.7            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 10               | F153AA275(1)050T      | MDC10275(1)50A52P3TUBE   |
| 50  | 30  | 3.3            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 8                | F153AA335(1)050T      | MDC10335(1)50A52P3TUBE   |
| 50  | 30  | 3.9            | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 7                | F153AA395(1)050T      | MDC10395(1)50A52P3TUBE   |
| 50  | 30  | 8.2            | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 4                | F15(4)AA685(1)050T    | MDC10825(1)50A58P(4)TUBE |
| 50  | 30  | 10             | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 3                | F15(4)AA106(1)050T    | MDC10106(1)50A58P(4)TUBE |
| 50  | 30  | 12             | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 3                | F15(4)AA126(1)050T    | MDC10126(1)50A58P(4)TUBE |
| 50  | 30  | 0.033          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 390              | F153BA333(1)050T      | MDC15333(1)50B53P3TUBE   |
| 50  | 30  | 0.039          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 330              | F153BA393(1)050T      | MDC15393(1)50B53P3TUBE   |
| 50  | 30  | 0.047          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 270              | F153BA473(1)050T      | MDC15473(1)50B53P3TUBE   |
| 50  | 30  | 0.056          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 230              | F153BA563(1)050T      | MDC15563(1)50B53P3TUBE   |
| 50  | 30  | 0.068          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 190              | F153BA683(1)050T      | MDC15683(1)50B53P3TUBE   |
| 50  | 30  | 0.082          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 160              | F153BA823(1)050T      | MDC15823(1)50B53P3TUBE   |
| 50  | 30  | 0.10           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 130              | F153BA104(1)050T      | MDC15104(1)50B53P3TUBE   |
| 50  | 30  | 0.12           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 110              | F153BA124(1)050T      | MDC15124(1)50B53P3TUBE   |
| 50  | 30  | 0.15           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 85               | F153BA154(1)050T      | MDC15154(1)50B53P3TUBE   |
| 50  | 30  | 0.18           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 70               | F153BA184(1)050T      | MDC15184(1)50B53P3TUBE   |
| 50  | 30  | 0.22           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 58               | F153BA224(1)050T      | MDC15224(1)50B53P3TUBE   |
| 50  | 30  | 0.27           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 47               | F153BA274(1)050T      | MDC15274(1)50B53P3TUBE   |
| 50  | 30  | 0.33           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 39               | F153BA334(1)050T      | MDC15334(1)50B53P3TUBE   |
| 50  | 30  | 0.39           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 39               | F153BA394(1)050T      | MDC15394(1)50B53P3TUBE   |
| 50  | 30  | 0.47           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 30               | F153BA474(1)050T      | MDC15474(1)50B53P3TUBE   |
| 50  | 30  | 0.56           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 26               | F153BA564(1)050T      | MDC15564(1)50B53P3TUBE   |
| 50  | 30  | 0.68           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 21               | F153BA684(1)050T      | MDC15684(1)50B53P3TUBE   |
| 50  | 30  | 0.82           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 18               | F153BA824(1)050T      | MDC15824(1)50B53P3TUBE   |
| 50  | 30  | 1.0            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 15               | F153BA105(1)050T      | MDC15105(1)50B53P3TUBE   |
| 50  | 30  | 1.2            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 15               | F153BA125(1)050T      | MDC15125(1)50B53P3TUBE   |
| 50  | 30  | 1.5            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 13               | F153BA155(1)050T      | MDC15155(1)50B53P3TUBE   |
| 50  | 30  | 1.8            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 13               | F153BA185(1)050T      | MDC15185(1)50B53P3TUBE   |
| 50  | 30  | 2.2            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 11               | F153BA225(1)050T      | MDC15225(1)50B53P3TUBE   |
| 50  | 30  | 2.7            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 11               | F153BA275(1)050T      | MDC15275(1)50B53P3TUBE   |
| 50  | 30  | 3.3            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 8                | F153BA335(1)050T      | MDC15335(1)50B53P3TUBE   |
| 50  | 30  | 3.9            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 8                | F153BA395(1)050T      | MDC15395(1)50B53P3TUBE   |
| 50  | 30  | 4.7            | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 6                | F153BA475(1)050T      | MDC15475(1)50B53P3TUBE   |
| 100 | 63  | 0.033          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 390              | F153AA333(1)100T      | MDC10333(1)100A52P3TUBE  |
| VDC | VAC | Cap Value (µF) | Size Code (New/Legacy)  | B (mm)           | H (mm) | L (mm) | Lead Spacing (p) | ESR 500 kHz (mΩ) | New KEMET Part Number | Legacy Part Number       |

(1) J = ±5%, K = ±10%, other tolerances on request.

(2) = Number of leads per side, 3 or 4.

(3) = Number of leads per side, 3, 4 or 5.

(4) = Number of leads per side, 7 or 8.

**Surface Mount Polyester (PET) Film Capacitor**  
**MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)**

**Table 1 – Ratings & Part Number Reference cont.**

| VDC | VAC | Cap Value<br>(µF) | Size Code<br>(New/<br>Legacy) | Dimensions in<br>mm |        |        | Lead<br>Spacing<br>(p) | ESR 500<br>kHz (mΩ) | New KEMET<br>Part Number | Legacy<br>Part Number     |
|-----|-----|-------------------|-------------------------------|---------------------|--------|--------|------------------------|---------------------|--------------------------|---------------------------|
|     |     |                   |                               | B                   | H      | L      |                        |                     |                          |                           |
| 100 | 63  | 0.039             | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 330                 | F153AA393(1)100T         | MDC10393(1)100A52P3TUBE   |
| 100 | 63  | 0.047             | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 270                 | F153AA473(1)100T         | MDC10473(1)100A52P3TUBE   |
| 100 | 63  | 0.056             | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 230                 | F153AA563(1)100T         | MDC10563(1)100A52P3TUBE   |
| 100 | 63  | 0.068             | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 190                 | F153AA683(1)100T         | MDC10683(1)100A52P3TUBE   |
| 100 | 63  | 0.082             | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 160                 | F153AA823(1)100T         | MDC10823(1)100A52P3TUBE   |
| 100 | 63  | 0.10              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 130                 | F153AA104(1)100T         | MDC10104(1)100A52P3TUBE   |
| 100 | 63  | 0.12              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 110                 | F153AA124(1)100T         | MDC10124(1)100A52P3TUBE   |
| 100 | 63  | 0.15              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 85                  | F153AA154(1)100T         | MDC10154(1)100A52P3TUBE   |
| 100 | 63  | 0.18              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 70                  | F153AA184(1)100T         | MDC10184(1)100A52P3TUBE   |
| 100 | 63  | 0.22              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 58                  | F153AA224(1)100T         | MDC10224(1)100A52P3TUBE   |
| 100 | 63  | 0.27              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 47                  | F153AA274(1)100T         | MDC10274(1)100A52P3TUBE   |
| 100 | 63  | 0.33              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 39                  | F153AA334(1)100T         | MDC10334(1)100A52P3TUBE   |
| 100 | 63  | 0.39              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 33                  | F153AA394(1)100T         | MDC10394(1)100A52P3TUBE   |
| 100 | 63  | 0.47              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 30                  | F153AA474(1)100T         | MDC10474(1)100A52P3TUBE   |
| 100 | 63  | 0.56              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 26                  | F153AA564(1)100T         | MDC10564(1)100A52P3TUBE   |
| 100 | 63  | 0.68              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 21                  | F153AA684(1)100T         | MDC10684(1)100A52P3TUBE   |
| 100 | 63  | 0.82              | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 18                  | F153AA824(1)100T         | MDC10824(1)100A52P3TUBE   |
| 100 | 63  | 1.0               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 15                  | F153AA105(1)100T         | MDC10105(1)100A52P3TUBE   |
| 100 | 63  | 1.2               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 14                  | F153AA125(1)100T         | MDC10125(1)100A52P3TUBE   |
| 100 | 63  | 1.5               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 13                  | F153AA155(1)100T         | MDC10155(1)100A52P3TUBE   |
| 100 | 63  | 1.8               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 12                  | F153AA185(1)100T         | MDC10185(1)100A52P3TUBE   |
| 100 | 63  | 2.2               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 11                  | F153AA225(1)100T         | MDC10225(1)100A52P3TUBE   |
| 100 | 35  | 2.7               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 10                  | F153AA275(1)100T         | MDC10275(1)100A52P3TUBE   |
| 100 | 35  | 3.3               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 8                   | F153AA335(1)100T         | MDC10335(1)100A52P3TUBE   |
| 100 | 35  | 3.9               | AA/A52                        | 12.2                | 5.75   | 11.0   | 10                     | 7                   | F153AA395(1)100T         | MDC10395(1)100A52P3TUBE   |
| 100 | 35  | 4.7               | AA/A54                        | 12.2                | 5.75   | 13.5   | 10                     | 6                   | F15(2)AA475(1)100T       | MDC10475(1)100A54P(2)TUBE |
| 100 | 35  | 4.7               | AA/A53                        | 12.7                | 8.5    | 14.0   | 10                     | 6                   | F15(2)AA475(1)100VV687   | MDC10475(1)100A53P(2)TR32 |
| 100 | 63  | 6.8               | AA/A58                        | 12.7                | 10.5   | 23.0   | 10                     | 5                   | F15(4)AA685(1)100T       | MDC10685(1)100A58P(4)TUBE |
| 100 | 63  | 8.2               | AA/A58                        | 12.7                | 10.5   | 23.0   | 10                     | 4                   | F15(4)AA825(1)100T       | MDC10825(1)100A58P(4)TUBE |
| 100 | 63  | 10                | AA/A58                        | 12.7                | 10.5   | 23.0   | 10                     | 3                   | F15(4)AA106(1)100T       | MDC10106(1)100A58P(4)TUBE |
| 100 | 63  | 0.033             | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 390                 | F153BA333(1)100T         | MDC15333(1)100B53P3TUBE   |
| 100 | 63  | 0.039             | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 330                 | F153BA393(1)100T         | MDC15393(1)100B53P3TUBE   |
| 100 | 63  | 0.047             | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 270                 | F153BA473(1)100T         | MDC15473(1)100B53P3TUBE   |
| 100 | 63  | 0.056             | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 230                 | F153BA563(1)100T         | MDC15563(1)100B53P3TUBE   |
| 100 | 63  | 0.068             | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 190                 | F153BA683(1)100T         | MDC15683(1)100B53P3TUBE   |
| 100 | 63  | 0.082             | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 160                 | F153BA823(1)100T         | MDC15823(1)100B53P3TUBE   |
| 100 | 63  | 0.10              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 130                 | F153BA104(1)100T         | MDC15104(1)100B53P3TUBE   |
| 100 | 63  | 0.12              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 110                 | F153BA124(1)100T         | MDC15124(1)100B53P3TUBE   |
| 100 | 63  | 0.15              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 85                  | F153BA154(1)100T         | MDC15154(1)100B53P3TUBE   |
| 100 | 63  | 0.18              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 70                  | F153BA184(1)100T         | MDC15184(1)100B53P3TUBE   |
| 100 | 63  | 0.22              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 58                  | F153BA224(1)100T         | MDC15224(1)100B53P3TUBE   |
| 100 | 63  | 0.27              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 47                  | F153BA274(1)100T         | MDC15274(1)100B53P3TUBE   |
| 100 | 63  | 0.33              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 39                  | F153BA334(1)100T         | MDC15334(1)100B53P3TUBE   |
| 100 | 63  | 0.39              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 39                  | F153BA394(1)100T         | MDC15394(1)100B53P3TUBE   |
| 100 | 63  | 0.47              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 30                  | F153BA474(1)100T         | MDC15474(1)100B53P3TUBE   |
| 100 | 63  | 0.56              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 26                  | F153BA564(1)100T         | MDC15564(1)100B53P3TUBE   |
| 100 | 63  | 0.68              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 21                  | F153BA684(1)100T         | MDC15684(1)100B53P3TUBE   |
| 100 | 63  | 0.82              | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 18                  | F153BA824(1)100T         | MDC15824(1)100B53P3TUBE   |
| 100 | 63  | 1.0               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 15                  | F153BA105(1)100T         | MDC15105(1)100B53P3TUBE   |
| 100 | 63  | 1.2               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 15                  | F153BA125(1)100T         | MDC15125(1)100B53P3TUBE   |
| 100 | 63  | 1.5               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 13                  | F153BA155(1)100T         | MDC15155(1)100B53P3TUBE   |
| 100 | 63  | 1.8               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 13                  | F153BA185(1)100T         | MDC15185(1)100B53P3TUBE   |
| 100 | 63  | 2.2               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 11                  | F153BA225(1)100T         | MDC15225(1)100B53P3TUBE   |
| 100 | 63  | 2.7               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 11                  | F153BA275(1)100T         | MDC15275(1)100B53P3TUBE   |
| 100 | 63  | 3.3               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 8                   | F153BA335(1)100T         | MDC15335(1)100B53P3TUBE   |
| 100 | 63  | 3.9               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 8                   | F153BA395(1)100T         | MDC15395(1)100B53P3TUBE   |
| 100 | 35  | 4.7               | BA/B53                        | 16.5                | 5.75   | 11.0   | 15                     | 6                   | F153BA475(1)100T         | MDC15475(1)100B53P3TUBE   |
| VDC | VAC | Cap Value<br>(µF) | Size Code<br>(New/Legacy)     | B (mm)              | H (mm) | L (mm) | Lead<br>Spacing (p)    | ESR 500<br>kHz (mΩ) | New KEMET<br>Part Number | Legacy<br>Part Number     |

(1) J = ±5%, K = ±10%, other tolerances on request.

(2) = Number of leads per side, 3 or 4.

(3) = Number of leads per side, 3, 4 or 5.

(4) = Number of leads per side, 7 or 8.



Surface Mount Polyester (PET) Film Capacitor  
MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

Table 1 – Ratings & Part Number Reference cont.

| VDC | VAC | Cap Value (µF) | Size Code (New/ Legacy) | Dimensions in mm |        |        | Lead Spacing (p) | ESR 500 kHz (mΩ) | New KEMET Part Number | Legacy Part Number        |
|-----|-----|----------------|-------------------------|------------------|--------|--------|------------------|------------------|-----------------------|---------------------------|
|     |     |                |                         | B                | H      | L      |                  |                  |                       |                           |
| 250 | 160 | 0.033          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 390              | F153AA333(1)250T      | MDC10333(1)250A52P3TUBE   |
| 250 | 160 | 0.039          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 330              | F153AA393(1)250T      | MDC10393(1)250A52P3TUBE   |
| 250 | 160 | 0.047          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 270              | F153AA473(1)250T      | MDC10473(1)250A52P3TUBE   |
| 250 | 160 | 0.056          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 230              | F153AA563(1)250T      | MDC10563(1)250A52P3TUBE   |
| 250 | 160 | 0.068          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 190              | F153AA683(1)250T      | MDC10683(1)250A52P3TUBE   |
| 250 | 160 | 0.082          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 160              | F153AA823(1)250T      | MDC10823(1)250A52P3TUBE   |
| 250 | 160 | 0.10           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 130              | F153AA104(1)250T      | MDC10104(1)250A52P3TUBE   |
| 250 | 160 | 0.12           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 130              | F153AA124(1)250T      | MDC10124(1)250A52P3TUBE   |
| 250 | 160 | 0.15           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 130              | F153AA154(1)250T      | MDC10154(1)250A52P3TUBE   |
| 250 | 160 | 0.18           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 70               | F153AA184(1)250T      | MDC10184(1)250A52P3TUBE   |
| 250 | 160 | 0.22           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 58               | F153AA224(1)250T      | MDC10224(1)250A52P3TUBE   |
| 250 | 160 | 0.27           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 47               | F153AA274(1)250T      | MDC10274(1)250A52P3TUBE   |
| 250 | 160 | 0.33           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 39               | F153AA334(1)250T      | MDC10334(1)250A52P3TUBE   |
| 250 | 160 | 0.39           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 33               | F153AA394(1)250T      | MDC10394(1)250A52P3TUBE   |
| 250 | 160 | 0.47           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 30               | F153AA474(1)250T      | MDC10474(1)250A52P3TUBE   |
| 250 | 160 | 0.56           | AA/A54                  | 12.2             | 5.75   | 13.5   | 10               | 26               | F15(2)AA564(1)250T    | MDC10564(1)250A52P3TUBE   |
| 250 | 160 | 0.82           | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 18               | F15(4)AA824(1)250T    | MDC10824(1)250A58P(4)TUBE |
| 250 | 160 | 1.0            | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 15               | F15(4)AA105(1)250T    | MDC10105(1)250A58P(4)TUBE |
| 250 | 160 | 1.2            | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 14               | F15(4)AA125(1)250T    | MDC10125(1)250A58P(4)TUBE |
| 250 | 160 | 1.5            | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 13               | F15(4)AA155(1)250T    | MDC10155(1)250A58P(4)TUBE |
| 250 | 160 | 0.033          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 390              | F153BA333(1)250T      | MDC15333(1)250B53P3TUBE   |
| 250 | 160 | 0.039          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 330              | F153BA393(1)250T      | MDC15393(1)250B53P3TUBE   |
| 250 | 160 | 0.047          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 270              | F153BA473(1)250T      | MDC15473(1)250B53P3TUBE   |
| 250 | 160 | 0.056          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 230              | F153BA563(1)250T      | MDC15563(1)250B53P3TUBE   |
| 250 | 160 | 0.068          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 190              | F153BA683(1)250T      | MDC15683(1)250B53P3TUBE   |
| 250 | 160 | 0.082          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 160              | F153BA823(1)250T      | MDC15823(1)250B53P3TUBE   |
| 250 | 160 | 0.10           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 130              | F153BA104(1)250T      | MDC15104(1)250B53P3TUBE   |
| 250 | 160 | 0.12           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 110              | F153BA124(1)250T      | MDC15124(1)250B53P3TUBE   |
| 250 | 160 | 0.15           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 85               | F153BA154(1)250T      | MDC15154(1)250B53P3TUBE   |
| 250 | 160 | 0.18           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 70               | F153BA184(1)250T      | MDC15184(1)250B53P3TUBE   |
| 250 | 160 | 0.22           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 58               | F153BA224(1)250T      | MDC15224(1)250B53P3TUBE   |
| 250 | 160 | 0.27           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 47               | F153BA274(1)250T      | MDC15274(1)250B53P3TUBE   |
| 250 | 160 | 0.33           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 39               | F153BA334(1)250T      | MDC15334(1)250B53P3TUBE   |
| 250 | 160 | 0.39           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 39               | F153BA394(1)250T      | MDC15394(1)250B53P3TUBE   |
| 250 | 160 | 0.47           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 30               | F153BA474(1)250T      | MDC15474(1)250B53P3TUBE   |
| 250 | 160 | 0.56           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 26               | F153BA564(1)250T      | MDC15564(1)250B53P3TUBE   |
| 250 | 160 | 0.68           | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 21               | F153BA684(1)250T      | MDC15684(1)250B53P3TUBE   |
| 400 | 200 | 0.033          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 390              | F153AA333(1)400T      | MDC10333(1)400A52P3TUBE   |
| 400 | 200 | 0.039          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 330              | F153AA393(1)400T      | MDC10393(1)400A52P3TUBE   |
| 400 | 200 | 0.047          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 270              | F153AA473(1)400T      | MDC10473(1)400A52P3TUBE   |
| 400 | 200 | 0.056          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 230              | F153AA563(1)400T      | MDC10563(1)400A52P3TUBE   |
| 400 | 200 | 0.068          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 190              | F153AA683(1)400T      | MDC10683(1)400A52P3TUBE   |
| 400 | 200 | 0.082          | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 160              | F153AA823(1)400T      | MDC10823(1)400A52P3TUBE   |
| 400 | 200 | 0.10           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 130              | F153AA104(1)400T      | MDC10104(1)400A52P3TUBE   |
| 400 | 200 | 0.12           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 110              | F153AA124(1)400T      | MDC10124(1)400A52P3TUBE   |
| 400 | 200 | 0.15           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 85               | F153AA154(1)400T      | MDC10154(1)400A52P3TUBE   |
| 400 | 200 | 0.18           | AA/A52                  | 12.2             | 5.75   | 11.0   | 10               | 70               | F153AA184(1)400T      | MDC10184(1)400A52P3TUBE   |
| 400 | 200 | 0.22           | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 58               | F15(4)AA224(1)400T    | MDC10224(1)400A58P(4)TUBE |
| 400 | 200 | 0.27           | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 47               | F15(4)AA274(1)400T    | MDC10274(1)400A58P(4)TUBE |
| 400 | 200 | 0.33           | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 39               | F15(4)AA334(1)400T    | MDC10334(1)400A58P(4)TUBE |
| 400 | 200 | 0.39           | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 33               | F15(4)AA394(1)400T    | MDC10394(1)400A58P(4)TUBE |
| 400 | 200 | 0.47           | AA/A58                  | 12.7             | 10.5   | 23.0   | 10               | 30               | F15(4)AA474(1)400T    | MDC10474(1)400A58P(4)TUBE |
| 400 | 200 | 0.033          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 390              | F153BA333(1)400T      | MDC15333(1)400B53P3TUBE   |
| 400 | 200 | 0.039          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 330              | F153BA393(1)400T      | MDC15393(1)400B53P3TUBE   |
| 400 | 200 | 0.047          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 270              | F153BA473(1)400T      | MDC15473(1)400B53P3TUBE   |
| 400 | 200 | 0.056          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 230              | F153BA563(1)400T      | MDC15563(1)400B53P3TUBE   |
| 400 | 200 | 0.068          | BA/B53                  | 16.5             | 5.75   | 11.0   | 15               | 190              | F153BA683(1)400T      | MDC15683(1)400B53P3TUBE   |
| VDC | VAC | Cap Value (µF) | Size Code (New/Legacy)  | B (mm)           | H (mm) | L (mm) | Lead Spacing (p) | ESR 500 kHz (mΩ) | New KEMET Part Number | Legacy Part Number        |

(1) J = ±5%, K = ±10%, other tolerances on request.

(2) = Number of leads per side, 3 or 4.

(3) = Number of leads per side, 3, 4 or 5.

(4) = Number of leads per side, 7 or 8.



**Surface Mount Polyester (PET) Film Capacitor**  
**MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)**

**Table 1 – Ratings & Part Number Reference cont.**

| VDC | VAC | Cap Value (μF) | Size Code (New/Legacy) | Dimensions in mm |        |        | Lead Spacing (p) | ESR 500 kHz (mΩ) | New KEMET Part Number | Legacy Part Number        |
|-----|-----|----------------|------------------------|------------------|--------|--------|------------------|------------------|-----------------------|---------------------------|
|     |     |                |                        | B                | H      | L      |                  |                  |                       |                           |
| 400 | 200 | 0.082          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 160              | F153BA823(1)400T      | MDC15823(1)400B53P3TUBE   |
| 400 | 200 | 0.10           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 130              | F153BA104(1)400T      | MDC15104(1)400B53P3TUBE   |
| 400 | 200 | 0.12           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 110              | F153BA124(1)400T      | MDC15124(1)400B53P3TUBE   |
| 400 | 200 | 0.15           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 85               | F153BA154(1)400T      | MDC15154(1)400B53P3TUBE   |
| 400 | 200 | 0.18           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 70               | F153BA184(1)400T      | MDC15184(1)400B53P3TUBE   |
| 400 | 200 | 0.22           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 58               | F153BA224(1)400T      | MDC15224(1)400B53P3TUBE   |
| 400 | 200 | 0.27           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 47               | F153BA274(1)400T      | MDC15274(1)400B53P3TUBE   |
| 630 | 220 | 0.033          | AA/A52                 | 12.2             | 5.75   | 11.0   | 10               | 390              | F153AA333(1)630T      | MDC10333(1)630A52P3TUBE   |
| 630 | 220 | 0.039          | AA/A52                 | 12.2             | 5.75   | 11.0   | 10               | 330              | F153AA393(1)630T      | MDC10393(1)630A52P3TUBE   |
| 630 | 220 | 0.047          | AA/A52                 | 12.2             | 5.75   | 11.0   | 10               | 270              | F153AA473(1)630T      | MDC10473(1)630A52P3TUBE   |
| 630 | 220 | 0.056          | AA/A52                 | 12.2             | 5.75   | 11.0   | 10               | 230              | F153AA563(1)630T      | MDC10563(1)630A52P3TUBE   |
| 630 | 220 | 0.068          | AA/A54                 | 12.2             | 5.75   | 13.5   | 10               | 190              | F15(2)AA683(1)630T    | MDC10683(1)630A54P(2)TUBE |
| 630 | 220 | 0.082          | AA/A58                 | 12.7             | 10.5   | 23.0   | 10               | 160              | F15(4)AA823(1)630T    | MDC10823(1)630A58P(4)TUBE |
| 630 | 220 | 0.10           | AA/A58                 | 12.7             | 10.5   | 23.0   | 10               | 130              | F15(4)AA104(1)630T    | MDC10104(1)630A58P(4)TUBE |
| 630 | 220 | 0.12           | AA/A58                 | 12.7             | 10.5   | 23.0   | 10               | 110              | F15(4)AA124(1)630T    | MDC10124(1)630A58P(4)TUBE |
| 630 | 220 | 0.15           | AA/A58                 | 12.7             | 10.5   | 23.0   | 10               | 85               | F15(4)AA154(1)630T    | MDC10154(1)630A58P(4)TUBE |
| 630 | 220 | 0.18           | AA/A58                 | 12.7             | 10.5   | 23.0   | 10               | 70               | F15(4)AA184(1)630T    | MDC10184(1)630A58P(4)TUBE |
| 630 | 220 | 0.033          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 390              | F153BA333(1)630T      | MDC15333(1)630B53P3TUBE   |
| 630 | 220 | 0.039          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 330              | F153BA393(1)630T      | MDC15393(1)630B53P3TUBE   |
| 630 | 220 | 0.047          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 270              | F153BA473(1)630T      | MDC15473(1)630B53P3TUBE   |
| 630 | 220 | 0.056          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 230              | F153BA563(1)630T      | MDC15563(1)630B53P3TUBE   |
| 630 | 220 | 0.068          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 190              | F153BA683(1)630T      | MDC15683(1)630B53P3TUBE   |
| 630 | 220 | 0.082          | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 160              | F153BA823(1)630T      | MDC15823(1)630B53P3TUBE   |
| 630 | 220 | 0.10           | BA/B53                 | 16.5             | 5.75   | 11.0   | 15               | 130              | F153BA104(1)630T      | MDC15104(1)630B53P3TUBE   |
| VDC | VAC | Cap Value (μF) | Size Code (New/Legacy) | B (mm)           | H (mm) | L (mm) | Lead Spacing (p) | ESR 500 kHz (mΩ) | New KEMET Part Number | Legacy Part Number        |

(1) J = ±5%, K = ±10%, other tolerances on request.

(2) = Number of leads per side, 3 or 4.

(3) = Number of leads per side, 3, 4 or 5.

(4) = Number of leads per side, 7 or 8.


# Surface Mount Polyester (PET) Film Capacitor

MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)


## Soldering Process

**Reflow soldering temperature is measured on the top surface of the component:** Preheating temperature should be less than 170°C. The time above 217°C should be less than 50 seconds. The peak temperature must not exceed 240°C.

A lead-free soldering process for this series is in development. Please contact KEMET for details.




## Construction



Surface Mount Polyester (PET) Film Capacitor  
MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

Marking




| Manufacturing Date Code (IEC 60062) |      |           |      |
|-------------------------------------|------|-----------|------|
| Year                                | Code | Month     | Code |
| 2020                                | M    | January   | 1    |
| 2021                                | N    | February  | 2    |
| 2022                                | P    | March     | 3    |
| 2023                                | R    | April     | 4    |
| 2024                                | S    | May       | 5    |
| 2025                                | T    | June      | 6    |
| 2026                                | U    | July      | 7    |
| 2027                                | V    | August    | 8    |
| 2028                                | W    | September | 9    |
| 2029                                | X    | October   | 0    |
| 2030                                | A    | November  | N    |
| 2031                                | B    | December  | D    |
| 2032                                | C    |           |      |
| 2033                                | D    |           |      |
| 2034                                | E    |           |      |
| 2035                                | F    |           |      |
| 2036                                | H    |           |      |
| 2037                                | J    |           |      |
| 2038                                | K    |           |      |
| 2039                                | L    |           |      |
| 2040                                | M    |           |      |

Packaging Quantities

| Size Code | Lead Spacing | Base (mm) | Height (mm) | Length (mm) | Bulk | Reel |
|-----------|--------------|-----------|-------------|-------------|------|------|
| A52       | 10.0         | 12.2      | 5.75        | 11.0        | 43   | 200  |
| A53       |              | 12.7      | 8.5         | 14.0        | 34   |      |
| A54       |              | 12.2      | 5.75        | 13.5        | 35   |      |
| A55       |              | 12.2      | 5.75        | 16.5        | 28   |      |
| A58       |              | 12.7      | 10.5        | 23.0        | 21   |      |
| B53       | 15.0         | 16.5      | 5.75        | 11.0        | 43   |      |
| B55       |              | 16.5      | 5.75        | 12.2        | 39   |      |

Surface Mount Polyester (PET) Film Capacitor  
MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)


Tube Packaging



| Size Code | Dimensions in mm          | Tube   |
|-----------|---------------------------|--------|
| A52       | 10.0 – 12.2 x 5.75 x 11.0 | Tube B |
| A53       | 10.0 – 12.7 x 8.5 x 14.0  | Tube A |
| A54       | 10.0 – 12.2 x 5.75 x 13.5 | Tube B |
| A55       | 10.0 – 12.2 x 5.75 x 16.5 | Tube B |
| A58       | 10.0 – 12.7 x 10.5 x 23.0 | Tube A |
| B53       | 15.0 – 16.5 x 5.75 x 11.0 | Tube C |
| B55       | 15.0 – 16.5 x 5.75 x 12.2 | Tube C |

Landing

| Size | Dimensions in mm |   |   |       |       |      |      |
|------|------------------|---|---|-------|-------|------|------|
|      | p                | A | B | C     | D     | E    | F    |
| A52  | 10               | 1 | 2 | 9.15  | 13.15 | 2.54 | 0.25 |
| A53  | 10               | 1 | 2 | 9.15  | 13.15 | 2.54 | 0.25 |
| A54  | 10               | 1 | 2 | 9.15  | 13.15 | 2.54 | 0.25 |
| A55  | 10               | 1 | 2 | 9.15  | 13.15 | 2.54 | 0.25 |
| A58  | 10               | 1 | 2 | 9.15  | 13.15 | 2.54 | 0.25 |
| B53  | 15               | 1 | 2 | 14.15 | 18.15 | 2.54 | 0.25 |
| B55  | 15               | 1 | 2 | 14.15 | 18.15 | 2.54 | 0.25 |



# Surface Mount Polyester (PET) Film Capacitor

## MDC, Dual In-Line, 50 – 630 VDC, High Current(Automotive Grade)

### KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit <https://www.yageogroup.com/SalesResources/SalesOffices>

---

### Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

Additional information about production site flexibility can be found [here](#)

*KEMET is a registered trademark of KEMET Electronics Corporation.*