

# RF Inductor



## BWLS Series



### Overview

Wire-wound RF inductors are electronic components designed to store energy in a magnetic field when electrical current passes through them. They are constructed by winding a conductive wire (usually copper or gold-plated) around a core material such as air, ceramic, or ferrite.

This configuration allows them to provide high inductance values with minimal power loss, especially at high frequencies.

### Benefits

1. High Q-Factor (Quality Factor)
2. Ceramic body and wire wound construction provide high SRFs
3. Low DC resistance design
4. High Current Handling
5. Low inductance value

### Applications

1. Industrial and Medical Equipmen: RFID systems and medical imaging equipment.
2. Data Centers
3. Networking
4. Base Station
5. Consumer Electronics
6. Security system

### Product Information


Series	Size Code (JIS/EIA)	Inductance (nH)
BWLS	0603/0201	0.0047 ~ 560
	1005/0402	
	1608/0603	
	2012/0805	
	2520/1008	



## BWLS00302522 Series Specification

**1 Scope:** This specification applies to Wire Wound Ferrite Chip Inductors

**2 Part numbering:**




**3 Rating:**

Operating Temperature:  $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$   
(Including self - temperature rise)

Storage Temperature:  $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$   
(The storage temperature range is for after the assembly)

**4 Marking:**




**EX Marking:** 1st→BRN  
2st→RED  
3st→RED

**5 Standard Testing Condition**

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

## BWLS00302522 Series Specification

### 6 Configuration and Dimensions and Unit Weight:



Dimensions in mm

TYPE	A	B	C	D	E	F	G	H	I	J
302522	2.99Max.	2.5Max.	2.2 Max.	0.70	1.52	0.51	2.03	2.54	1.02	1.27

Net Weight (grms)

SIZE CODE	Net Weight (grms)
302522	0.035 (typ.)

### 7 Electrical Characteristics:

Part No.	Inductance (uH)	L/Q Test Freq. (MHz)	Q Typ.	SRF (MHz)Min.	RDC (Ω)Max.	IDC (mA)	Tolerance (±%)	Color Code		
								1st	2nd	3rd
BWLS003025221R2□00	1.2	7.9/50	55	350	0.5	1200	5,10	BRN	RED	RED
BWLS003025221R5□00	1.5	7.9/50	58	300	0.65	1200	5,10	BRN	GRN	RED
BWLS003025221R8□00	1.8	7.9/50	54	280	0.75	1050	5,10	BRN	GRY	RED
BWLS003025222R2□00	2.2	7.9/50	48	250	0.9	950	5,10	RED	RED	RED
BWLS003025222R7□00	2.7	7.9/50	51	200	1	950	5,10	RED	VIO	RED
BWLS003025223R3□00	3.3	7.9/50	58	200	1.15	900	5,10	ORN	ORN	RED
BWLS003025223R9□00	3.9	7.9/7.9	37	170	1.25	850	5,10	ORN	WHT	RED
BWLS003025224R7□00	4.7	7.9/7.9	37	130	1.35	700	5,10	YEL	VIO	RED
BWLS003025225R6□00	5.6	7.9/7.9	36	110	1.45	700	5,10	GRN	BLU	RED
BWLS003025226R8□00	6.8	7.9/7.9	33	105	1.6	600	5,10	BLU	GRY	RED
BWLS003025228R2□00	8.2	7.9/7.9	40	90	1.8	550	5,10	GRY	RED	RED
BWLS00302522100□00	10	7.9/7.9	40	85	2.4	500	5,10	BRN	BLK	ORN
BWLS00302522120□00	12	7.9/7.9	40	80	2.4	450	5,10	BRN	RED	ORN
BWLS00302522150□00	15	7.9/7.9	35	38	2.4	450	5,10	BRN	GRN	ORN
BWLS00302522390□00	39	2.5/2.5	33	26	10	170	5,10	ORN	WHT	ORN

**NOTE:** □-tolerance J=±5% / K=±10%

1. Operating temperature range - 40°C ~ 105°C


2. L/Q Test OSC @200mV.

3. IDC for Inductance drop 10% from its value without current.

## BWLS00302522 Series Specification

### 8 BWLS00302522 Series

#### 8.1 Construction:



#### 8.2 Material List:

NO	PART	MATERIAL
1	WIRE	COPPER 180
2	EPOXY	UV GLUE
3	CORE	FERRITE
4	TERMINAL	Ag/Cu/Ni/Sn

## BWLS00302522 Series Specification

### 9 Reliability Of Ferrite Wire Wound Chip Inductor/FERRITE SERIES


#### 1-1.Environmental Performance

No	Item	Specification	Test Method		
1-1-1	Temperature Cycle	Appearance: No Damage Inductance: within $\pm 10\%$ of initial value Q change: within $\pm 30\%$ of initial value	One cycle:		
			Step	Temperature ( $^{\circ}\text{C}$ )	Time (min)
			1	-40 $\pm$ 3	30
			2	25 $\pm$ 2	3
			3	105 $\pm$ 3	30
4	25 $\pm$ 2	3			
			Total: 5 cycles Measured After Exposure in The Room Condition For 1hrs		
1-1-2	High Temperature Resistance		Temperature: 85 $\pm$ 3 $^{\circ}\text{C}$ Time: 1000Hrs Measured After Exposure In The Room Condition For 1Hrs		
1-1-3	Low Temperature Resistance		Temperature: -25 $\pm$ 3 $^{\circ}\text{C}$ Time: 1000Hrs Measured After Exposure In The Room Condition For 1Hrs		
1-1-4	Humidity Load Life	There should be no evidence of short or open circle	Temperature: 40 $\pm$ 2 $^{\circ}\text{C}$ Relative Humidity: 90~95% Load: Allowed DC Current Time: 96Hrs		

#### 1-2.Mechanical Performance

No	Item	Specification	Test Method
1-2-1	Resistance TO Soldering Heat	Appearance: No Damage	1. The device should be reflow soldered on PCB (peak 260 $^{\circ}\text{C}$ $\pm$ 5 $^{\circ}\text{C}$ for 10 seconds) 2. Solder Composition: Sn/Ag3.0/Cu0.5 3. Test time: 6 minutes
1-2-2	Solder ability	The electrodes shall be at least 95% covered with new solder coating	1. Pre-Heating: 150 $^{\circ}\text{C}$ , 1min. 2. Solder Composition: Sn/Ag3.0/Cu0.5 3. Solder Temperature: 245 $\pm$ 5 $^{\circ}\text{C}$ . 4. Immersion Time: 4 $\pm$ 1 sec.
1-2-3	Component Adhesion (Push Test)	1 Lbs. For 0402 1 Lbs. For 0603 2 Lbs. For 201614 2 Lbs. For 0805 4 Lbs. For The Rest	The device should be reflow soldered (245 $\pm$ 5 $^{\circ}\text{C}$ For 10 seconds) to a tinned copper substrate. A force gauge should be applied to the side of the component. The device must withstand a minimum force of 1or2or4 pounds without a failure of the termination attached to component

## BWLS00302522 Series Specification



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升温區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	Above 217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	-	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	-
實際時間 Time result	-	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	-

**NOTE:**


- 1.Re-flow possible times : within 3 times
- 2.Nitrogen adopted is recommendes while in re-flow
- 3.Products can only be soldered with reflow

# BWLS00302522 Series Specification

## 10 Packaging:

### 10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



### 10.2 Packaging Quantity

TYPE	PCS/REEL
302522	2000

### 10.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
302522	178±1	60±0.5	12±0.5	1.5±0.5

## BWLS00302522 Series Specification

### 10 Packaging:


#### 10.4 Tape Dimensions in mm



#### Tape Material


Carrier tape : Polycarbonate

Cover tape : Polyethylene



TYPE	A	B	T	W	P	F	K
302522	2.40	2.93	0.26	8.0	4	3.5	2.25

### 11 Recommended Land Pattern:



Dimensions in mm









TYPE	H(In/mm)	I(In/mm)	J(In/mm)
302522	0.10/2.54	0.04/1.02	0.05/1.27

### 12 Note:

- Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- Do not knock nor drop.
- All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- The storage period is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% RH or less).  
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- The moisture sensitivity level (MSL) of products is classified as level 1.

# BWLS00302522 Series Specification

## 13 Graph:



# BWLS00302522 Series Specification

