

Rogowski - Current Sensor

RC01-SSS-0 Series
RC03-SSS-LLLL-0 Series
RC05-SSS-LLLL-0 Series



- Ⓢ Dynamic Range from 1 to 2500 Amps
- Ⓢ Meets IEC 61869-10 Accuracy Class 1
- Ⓢ Meets ANSI C12.20 Accuracy Class 1.0
- Ⓢ Phase error <0.03 degree @ 50 Hz / 60 Hz
- Ⓢ Bandwidth up to 50kHz
- Ⓢ Immune to external AC magnetic fields
- Ⓢ Immune to DC current & magnetic fields
- Ⓢ Low temperature coefficient

Electrical Specifications @ 25°C - Operating Temperature -20°C to +80°C

Description	Part Number	Sensitivity mV/kA			Wire length mm	typ. Resonance frequency kHz	typ. Temperature coefficient ppm / K	typ. external electromagnetic field %	typ. external electrical voltage potential mA (@230VAC / 50Hz)
		50 Hz	60 Hz	Tolerance					
RC01-SSS-0									
Rogowski Coil Size 01 - 100mV/kA	RC01-100	100	120	±1%	n.A.	370	30	0,2	60
Rogowski Coil Size 01 - 100mV/kA - Shielded	RC01-100-S								25
Rogowski Coil Size 01 - 200mV/kA	RC01-200	200	240	±1%	n.A.	200	25	0,2	40
Rogowski Coil Size 01 - 200mV/kA - Shielded	RC01-200-S								25
Rogowski Coil Size 01 - 300mV/kA	RC01-300	300	360	±1%	n.A.	150	25	0,2	35
Rogowski Coil Size 01 - 300mV/kA - Shielded	RC01-300-S								25
RC03-SSS-LLLL-0									
Rogowski Coil Size 03 - 200mV/kA	RC03-200-0250	200	240	±1%	250 ± 10	170	25	0,2	125
Rogowski Coil Size 03 - 200mV/kA - Shielded	RC03-200-0250-S								50
Rogowski Coil Size 03 - 400mV/kA	RC03-400-0250	400	480	±1%	250 ± 10	90	6	0,2	85
Rogowski Coil Size 03 - 400mV/kA - Shielded	RC03-400-0250-S								45
Rogowski Coil Size 03 - 600mV/kA	RC03-600-0250	600	720	±1%	250 ± 10	70	3	0,2	80
Rogowski Coil Size 03 - 600mV/kA - Shielded	RC03-600-0250-S								45
RC05-SSS-LLLL-0									
Rogowski Coil Size 05 - 150mV/kA	RC05-150-1000	150	180	±1%	1000 ± 20	110	28	0,2	140
Rogowski Coil Size 05 - 150mV/kA - Shielded	RC05-150-1000-S								20
Rogowski Coil Size 05 - 300mV/kA	RC05-300-1000	300	360	±1%	1000 ± 20	60	25	0,2	110
Rogowski Coil Size 05 - 300mV/kA - Shielded	RC05-300-1000-S								40
Rogowski Coil Size 05 - 450mV/kA	RC05-450-1000	450	540	±1%	1000 ± 20	45	21	0,2	80
Rogowski Coil Size 05 - 450mV/kA - Shielded	RC05-450-1000-S								20


Rogowski - Current Sensor

RC01-SSS-0 Series
 RC03-SSS-LLLL-0 Series
 RC05-SSS-LLLL-0 Series

Mechanicals


RC01-SSS-0

Weight: approx. 7g Dimensions in mm



polarity + : Pin 1
 polarity - : Pin 2
 shielding: Pin 3


Test setup for external electromagnetic field current conductor is close to the housing with the specified diameter.



Mechanicals


RC03-SSS-LLLL-0

Weight: approx. 23g (without cable) Dimensions in mm



polarity +: yellow
 polarity -: green
 shielding: blue

Test setup for external electromagnetic field current conductor is close to the housing with the specified diameter.



Rogowski - Current Sensor


RC01-SSS-0 Series
RC03-SSS-LLLL-0 Series
RC05-SSS-LLLL-0 Series

Mechanicals


RC05-SSS-LLLL-0

Weight: approx. 48g Dimensions in mm
(without cable)

polarity + : red
polarity - : black
shielding: blank



Test setup for external electromagnetic field current conductor is close to the housing with the specified diameter.



Codification

RCXX-SSS-LLLL-O

RC:
Rogowski Coil

XX:
01: Size 01
03: Size 03
05: Size 05

SSS:
Sensitivity in
mV/kA/50Hz

LLLL:
optional wire
length in mm

O: (Options)
S: with Shielding

For More Information:

info.egston@yageo.com | www.pulseelectronics.eu

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2021. Pulse Electronics, Inc. All rights reserved.