



Click [here](#) for the 3D model.

**General Information**

|                          |  |
|--------------------------|--|
| Series                   | T528   |
| Dielectric               | Polymer Tantalum                                 |
| Style                    | SMD Chip   |
| Description              | SMD, Polymer, Low ESR, NonCombustible, Face Down |
| Features                 | Face Down, Low ESR                               |
| RoHS                     | Yes  |
| Termination              | Tin  |
| Typical Component Weight | 206.33 mg  |
| Shelf Life               | 52 Weeks   |
| MSL                      | 3  |

**Dimensions**

|   |                |
|---|----------------|
| L | 7.3mm +/-0.4mm |
| W | 4.3mm +/-0.3mm |
| H | 1.6mm +/-0.1mm |
| S | 1.3mm +/-0.2mm |
| F | 2.8mm +/-0.2mm |
| R | 5mm +/-0.4mm   |

**Packaging Specifications**

|                    |            |
|--------------------|------------|
| Packaging          | T&R, 178mm |
| Packaging Quantity | 1000       |

**Specifications**

|                    |  |
|--------------------|--|
| Capacitance        | 330 uF   |
| Tolerance          | 20%  |
| Voltage DC         | 2.5 VDC (105C)   |
| Temperature Range  | -55/+105°C   |
| Rated Temperature  | 105°C  |
| Humidity           | 60C, 90% RH, no load, 500 Hours                                    |
| Dissipation Factor | 10% 120Hz 25C  |
| Failure Rate       | N/A  |
| ESR                | 5 mOhms (100kHz 25C)   |
| Ripple Current     | 8100 mA (rms, 100kHz 45C), 5670 mA (rms, 85C), 2025 mA (rms, 105C) |
| Leakage Current    | 82.5 uA (5min 25°C)  |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.