
Z1806C851BPWZT

Aliases (Z1806C851BPWZT)

Obsolete

EMI Suppression, KEMET, Z-PWZ, SMD Chip, Noise Suppression



Click here for the 3D model.

General Information	
Series	Z-PWZ
Style	SMD Chip
Description	Chip Bead, Power Line
Features	For MHz Range Applications
RoHS	Yes
Notes	Last Order Date June 30, 2023.

Dimensions	
L	4.5mm +/-0.3mm
W	1.6mm +/-0.2mm
T	1.6mm +/-0.2mm
B	0.5mm +/-0.3mm

Packaging Specifications	
Packaging	T&R
Packaging Quantity	2000

Specifications	
Impedance	850 Ohms (100 MHz)
Impedance Tolerance	30%
Ripple Current	1500 mA (MAX)
Temperature Range	-40/+125°C
DC Resistance	0.1 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO