

Power Inductor

Automotive Grade

APCA Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits


1. Automotive grade available
2. High break down voltage 1000V up
3. Operating temperature range - 40°C ~ 150°C
4. Fully automated production line

Applications

1. Automotive Systems for Infotainment, BCM, Dashboad, ADAS, Lamp
2. Media player, Audio class - D
3. Net working, LCD Panel/TV
4. IPC Equipment

Product Information

Series	L (mm)	W (mm)	T (mm)	Inductance (μH)
APCA	6.0	6.3	4.5	1 ~ 470
	7.0	7.4	4.5	
	10.3	10.0	6.5	
	12.5	12.3	8.0	




APCA00121280 Series Specification

AEC-Q200

1 Scope: This specification applies to the Pb Free high current type SMD inductors

2 Part Numbering:



3 Rating:

Operating Temperature: - 55°C ~ + 150°C (Including self temp. rise)




Storage Temperature: - 55°C ~ + 150°C (For after the circuit board is mounted)

Storage Temperature (on tape & reel): -20°C to +40°C; 75% RH max.

4 Standard Testing Condition:

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature (15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity (25 to 85% RH)	50 to 80 %RH

5 Configuration and Dimensions:



A:	12.5 ± 0.4	mm
B:	12.3 ± 0.4	mm
C:	8.0 Max.	mm
D:	4.0 Typ.	mm
E:	6.3 Typ.	mm
F:	3.15 Typ.	mm

Net Weight (grms)

SIZE CODE	Net Weight (grms)
121280	4.1(Typ.)

APCA00121280 Series Specification

AEC-Q200

6 Electrical Characteristics:


Part No.	Inductance L(μH)	Percent Tolerance	Test Frequency	Resistance RDC(Ω)	Rated DC Current		Marking
					Isat (A)	Irms (A)	
APCA001212801R5□80	1.5	T	100KHz/0.25V	5.5m ±30%	23.50	10.50	1R5
APCA001212802R2□80	2.2	T	100KHz/0.25V	6.3m ±30%	20.00	9.70	2R2
APCA001212803R3□80	3.3	T	100KHz/0.25V	7.7m ±30%	15.00	9.50	3R3
APCA001212804R7□80	4.7	T	100KHz/0.25V	8.7m ±30%	13.00	9.00	4R7
APCA001212806R8□80	6.8	T	100KHz/0.25V	10m ±20%	9.70	8.50	6R8
APCA00121280100□80	10	M,T	100KHz/0.25V	12m ±20%	9.20	7.70	100
APCA00121280150□80	15	M,T	100KHz/0.25V	24m ±20%	7.40	5.10	150
APCA00121280220□80	22	M,T	100KHz/0.25V	27m ±20%	5.80	4.50	220
APCA00121280330□80	33	M,T	100KHz/0.25V	52m ±20%	4.50	3.60	330
APCA00121280470□80	47	M,T	100KHz/0.25V	66m ±20%	4.20	3.20	470
APCA00121280680□80	68	M,T	100KHz/0.25V	90m ±20%	3.60	2.70	680
APCA00121280101□80	100	M,T	100KHz/0.25V	0.11 ±20%	2.90	2.60	101
APCA00121280151□80	150	M,T	100KHz/0.25V	0.17 ±20%	2.40	2.10	151
APCA00121280221□80	220	M,T	100KHz/0.25V	0.28 ±20%	1.95	1.60	221
APCA00121280331□80	330	M,T	100KHz/0.25V	0.41 ±20%	1.60	1.25	331
APCA00121280471□80	470	M,T	100KHz/0.25V	0.59 ±20%	1.30	1.10	471

NOTE: tolerance K = ±10% , M = ±20% , T = ±30%

1. Isat : Based on inductance change ($\Delta L/L_0$: drop 30% Typ.) @ ambient Temperature : 25°C

2. Irms : Based on temperature rise (ΔT : 40°C TYP.)

6.1 Construction:



6.2 Material List:

NO.	ITEM	DESCRIPTION & TYPE
1	CORE	FERRITE
2	WIRE	MAGNET WIRE (P180)
3	TERMINAL	Ag/Cu/Ni/Sn

APCA00121280 Series Specification

AEC-Q200

ELECTRICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Temperature characteristics	$\Delta L/L20^{\circ}\text{C} \leq \pm 10\%$ 0 ~ 2000 ppm/ $^{\circ}\text{C}$	The test shall be performed after the sample has stabilized in an ambient temperature of -20 to +85 $^{\circ}\text{C}$, and the value calculated based on the value applicable in a normal temperature and normal humidity shall be $\Delta L/L20^{\circ}\text{C} \leq \pm 10\%$.

MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
High Temperature Exposure (Storage)	1. $\Delta L/L0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	Refer to MIL-STD-202 Method 108 1. preconditioning : reflow 3 times. 2. 1000hrs. at rated operating temperature, part can be stored for 1000 hrs. @ 150 $^{\circ}\text{C}$. Unpowered. Measurement at 24 $\pm$ 4 hours after test conclusion.
Temperature Cycling	1. $\Delta L/L0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	Refer to JESD22 Method JA-104 1. preconditioning : reflow 3 times. 2. 1000 cycles (-55 $^{\circ}\text{C}$ to +150 $^{\circ}\text{C}$). Measurement at 24 $\pm$ 4 hours after test conclusion. 30min maximum dwell time at each temperature extreme. 1 min. maximum transition time.
Biased Humidity	1. $\Delta L/L0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	Refer to MIL-STD-202 Method 103 1. preconditioning : reflow 3 times. 2. 1000 hrs 85 $^{\circ}\text{C}$ /85%RH. Unpowered. Measurement at 24 $\pm$ 4 hours after test conclusion.
Operational Life	1. $\Delta L/L0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	Refer to MIL-PRF-27 1. preconditioning : reflow 3 times. 2. 1000 hrs. @ 150 $^{\circ}\text{C}$. Measurement 24 $\pm$ 4 hours after test conclusion.
Physical Dimensions	Product spec	Refer to JESD22-B100 Verify physical dimensions to the applicable device detail specification.

APCA00121280 Series Specification

AEC-Q200


MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Resistance to Solvent	1. Marking -No constitute failure 2. No damage or degradation that has occurred due to solvent	Refer to MIL-STD-202 Method 215 Immersion 3+0.5/-0 minutes in Terpene defluxer. Brush 10 strokes (wet bristle) 2 to 3 oz. Rinse in water. Air blow dry.
Mechanical Shock	1. $\Delta L/L_0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	MIL-STD-202 Method 213 Units are non-operating. Pulse shape : Half-sine waveform Impact acceleration : 100 g's Pulse duration : 6 ms Number of shocks : 18 shocks (3 shocks for each face)
Vibration	1. $\Delta L/L_0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	MIL-STD-202 Method 204 5 g's for 20 minutes, 12 cycles each of 3 orientations. Test from 10-2000Hz.
Resistance to Soldering Heat (reflow soldering)	1. $\Delta L/L_0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	Temperature profile of reflow soldering Refer to MIL-STD-202 Method 210 SMD: Condition K, time above 217°C, 60s – 150s, 3Cycles
Solderability	All terminations shall exhibit a continuous solder coating free from defects for a minimum of 95% of the critical area of any individual termination.	Refer to J-STD-002 For both Leaded & SMD. Electrical Test not required. Test Method B @ 245±5°C, dwell for 5+0/-0.5 seconds

APCA00121280 Series Specification


AEC-Q200

MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Board Flex	1. $\Delta L/L_0 \leq \pm 10\%$ 2. No Crack	Refer to AEC-Q200-005 Bend the board (D) X = 2mm, 60sec minimum holding time. 
Terminal Strength	1. $\Delta L/L_0 \leq \pm 10\%$ 2. Appearance-No damage (OM)	Refer to AEC-Q200-006 Apply a 1.8Kg force to the side of a device bending tested. The force shall be applied for 60+1 seconds.
Electrical Characterization	User Specification.	Parametrically test per lot and sample size requirements. Summary to show minimum, maximum, mean and standard deviation at room, minimum and maximum operating temperatures.
ESD		Refer to AEC-Q200-002 or ISO/DIS 10605 Refer to attachment third party report
Flammability	The marking and A side have no obvious broken, and the marking are clearly	Refer to UL 94 Burning stops within 10 seconds on a vertical specimen; drips of particles allowed as long as they are not inflamed.

7 Packaging:


7.1 Packaging -Cover Tape



7.2 Packaging Quantity


TYPE	PCS/REEL
APCA00121280	400

7.3 Reel Dimensions





7 Packaging:

7.4 Tape Dimensions in mm




**Unreeling
Direction**



8 Recommended Land Pattern:

(STANDARD PATTERN) Unit : mm



9 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock or drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components
(refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.
6. Suggestion

On customer side this product series need to be fixed by the glue after IR reflow.

Please refer to below example photo:



Glue