

EMI Common Mode Choke



BPPM Series



Overview

An EMI common mode choke (CMC) for power lines is a passive component specifically designed to suppress electromagnetic interference (EMI) in power supply circuits. A full series of common mode choke is designed for excellent noise attenuation with compact sizing for use in wide range of applications. Both standard series and custom designs are available.

Benefits

1. For DC Power Line Common Mode Filter
2. Miniature SMD type common mode filter for fully automated assembly
3. Wide impedance range ($70\Omega \sim 3000\Omega$) for EMI suppression
4. Operating temperature range $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$
4. Excellent solderability

Applications

1. Networking
2. EMI solutions for charger
3. Media player, Dashboard

Product Information

Series	Size Code (JIS/EIA)	Impedance(Ω)
BPPM	5050/2020	70 ~ 3000
	7060/2824	
	9070/3628	
	1211/4844	
	1513/6052	
	4850/1920	




BPPM00151360 Series Specification

6 Electrical Characteristics:

PT/NO.	Impedance(Ω) at 100MHz		Test Frequency	Resistance RDC(m Ω) Max.(1 line)	Rated Current (A) Max.	Insulation Resistance (M Ω) Min.	Rated Voltage (V)Max.
	Min.	Typ.					
BPPM00151360301X00	250	300	100MHz	4.7 Max.	13	10	125
BPPM00151360551X00	450	550	100MHz	3.8 $\pm$ 20%	10	10	125
BPPM00151360701X00	500	700	100MHz	7.0 Max.	10	10	125
BPPM00151360102X00	600	1000	100MHz	9.0 Max.	8.5	10	125
BPPM00151360152X00	1100	1500	50MHz	9.0 Max.	8.5	10	125
BPPM00151360232X00	1800	2300	50MHz	11.0 Max.	7.0	10	125
BPPM00151360322X00	2700	3200	40MHz	15.5 Max.	6.0	10	125
BPPM00151360432X00	3700	4300	30MHz	21.0 Max.	5.0	10	125

CIRCUIT DIAGRAM



NOTE:


1.Rated DC Current : Based on temperature rise (ΔT : 40 $^{\circ}$ C Typ.)

BPPM00151360 Series Specification

6 Electrical Characteristics:


(6)-1 Impedance

Measured by HP4291B RF Impedance Analyzer.



(6)-2 DC Resistance


Measured by Chroma 16502 milliohm meter.



(6)-3 Insulation Resistance


Measured by Chroma 19073

Measurement voltage : 50V ,Measurement time : 3 sec.



BPPM00151360 Series Specification

6.1 Construction:






6.2 Material List:

NO.	ITEM	DESCRIPTION & TYPE
1	CORE	FERRITE
2	Wire	Magnet Wire
3	Cover	Mayler
4	Marking	INK


BPPM00151360 Series Specification

MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Solder ability	The product shall be connected to the test circuit board by the fillet (the height is 0.2mm).	Apply cream solder to the printed circuit board . Refer to clause 8 for Reflow profile.
Resistance to Soldering heat (reflow soldering)	There shall be no damage or problems.	Temperature profile of reflow soldering  Note: 1. Re-Flow Possible times: within 2 times 2. Nitrogen adopted is recommended while in re-flow
Terminal strength	The terminal electrode and the ferrite must not be damaged.	Solder a chip to test substrate , and then laterally apply a load 9.8N in the arrow direction. 
Strength on PC board bending	The terminal electrode and the ferrite must not be damaged.	Solder a chip to test substrate and then apply a load. 
High temperature resistance	Impedance: Within $\pm 20\%$ of the initial value. Insulation resistance and DC resistance on the specification (refer to clause 2-1) shall be met. The terminal electrode and the ferrite must not be damaged.	After the samples shall be soldered onto the test circuit board, the test shall be done. Measurement : After placing for 24 hours min. Temperature : $+125 \pm 2^\circ\text{C}$ Testing time : 500 ± 12 hours

BPPM00151360 Series Specification


MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Humidity Bias	Impedance: Within $\pm 20\%$ of the initial value. Insulation resistance and DC resistance on the specification shall be met. The terminal electrode and the ferrite must not be damaged.	Precondition: Reflow peak temperature 260°C 3 times. (Reference: J-STD-020) 1000 hours $85^{\circ}\text{C}/85\%\text{RH}$. Unpowered. Measurement at 24 ± 4 hours after test conclusion.
Thermal shock	Impedance: Within $\pm 20\%$ of the initial value. Insulation resistance and DC resistance on the specification (refer to clause 2-1) shall be met. The terminal electrode and the ferrite must not be damaged.	 Testing Time: 100 cycle
Low temperature storage	Impedance: Within $\pm 20\%$ of the initial value. Insulation resistance and DC resistance on the specification (refer to clause 2-1) shall be met. The terminal electrode and the ferrite must not be damaged.	After the samples shall be soldered onto the test circuit board, the test shall be done. Measurement : After placing for 24 hours min. Temperature : $-40 \pm 2^{\circ}\text{C}$ Testing time : 500 ± 12 hours
Vibration	Impedance: Within $\pm 20\%$ of the initial value. Insulation resistance and DC resistance on the specification (refer to clause 2-1) shall be met. The terminal electrode and the ferrite must not be damaged.	After the samples shall be soldered onto the test circuit board, the test shall be done. Frequency : 10 to 55 Hz Amplitude : 1.52 mm Dimension and times : X, Y and Z directions for 2 hours each.
Solderability	New solder More than 75%	Flux (rosin, isopropyl alcohol (JIS-K-1522)) shall be coated over the whole of the sample before hand, the sample shall then be preheated for about 2 minutes in a temperature of $130 \sim 150^{\circ}\text{C}$ and after it has been immersed to a depth 0.5mm below for 3 ± 0.2 seconds fully in molten solder M705 with a temperature of $245 \pm 2^{\circ}\text{C}$. More than 75% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.

BPPM00151360 Series Specification

7 Packaging:

7.1 Packaging -Cover Tape




7.2 Packaging Quantity

TYPE	PCS/REEL
BPPM00151360	450

7.3 Reel Dimensions


Unit : mm





BPPM00151360 Series Specification

7 Packaging:

7.4 Tape Dimensions in mm




Unreeling
Direction



8 Recommended Land Pattern:

(STANDARD PATTERN) Unit : mm



BPPM00151360 Series Specification



9 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock or drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components
(refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.

BPPM00151360 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS



Frequency vs impedance



BPPM00151360 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS



Frequency vs impedance



BPPM00151360 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

Frequency vs impedance



BPPM00151360 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

Frequency vs impedance

