

BWVS Series



Overview

BWVS series are an automatic assembly constructed power inductor, is shielded with magnetic resin and suitable for portable DC-DC converter application.

Benefits

- 1. Shielded with magnetic resin
- 2. Low profile, miniature package size and wide inductance range
- 3. Low DCR and high rated current

Applications

- 1. Smartphones, tablets and wearable devices, Game consoles
- 2. DSC, camcorders
- 3. AP Routers, STBs
- 4. LCD TVs, monitors and panels
- 5. DC/DC converters

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BWVS	3.2	2.5	1.5	0.22 ~ 1200
	3.2	2.5	1.5	
	4.0	4.0	1.2	
	4.0	4.0	1.5~2.0	
	4.0	4.0	2.6	
	5.0	5.0	1.7~2.2	
	5.0	5.0	4.0	
	5.0	5.0	3.7~4.2	
	6.0	6.0	1.7~2.2	
	6.0	6.0	2.5~3.0	
	6.0	6.0	4.2~4.7	
	6.0	6.0	4.5	
	8.0	8.0	3.7~4.2	
	8.0	8.0	4.0	



BWVS00322515 Series Specification

1 Scope: This specification applies to Wire Wound Power Inductors

2 Part Numbering:




3 Rating:

Operating Temperature: $-55^{\circ}\text{C} \sim 125^{\circ}\text{C}$
(Including self - temperature rise)

Storage Temperature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
(The storage temperature range is for after the assembly)

4 Marking:



Ex Marking : 150


Marking color : Black

5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

BWVS00322515 Series Specification

6 Configuration and Dimensions:



Dimensions in mm

TYPE	322515
A	3.2±0.2
B	2.5±0.2
C	1.5±0.2
D	1.0typ

Net Weight (grms)

SIZE CODE	Net Weight (grms)
322515	0.048 (typ).

7 Electrical Characteristics:

Part No.	Inductance (uH)	Test Freq.	SRF (MHZ)Min.	RDC (mΩ)±20%	Isat(A) Typ.(Max)	Irms(A) Typ.(Max)	Tolerance (±%)	Marking
BWVS00322515R22□00	0.22	1MHz,1V	300	22	4.5(4.0)	2.9(2.6)	20,30	R22
BWVS00322515R47□00	0.47	1MHz,1V	168	27	3.4(3.0)	2.6(2.3)	20,30	R47
BWVS003225151R0□00	1.0	1MHz,1V	95	40	2.3(2.0)	2.2(2.0)	20,30	1R0
BWVS003225151R5□00	1.5	1MHz,1V	81	47	1.8(1.6)	2.1(1.9)	20,30	1R5
BWVS003225152R2□00	2.2	1MHz,1V	60	57	1.6(1.4)	1.9(1.7)	20,30	2R2
BWVS003225152R7□00	2.7	1MHz,1V	54	70	1.4(1.2)	1.7(1.5)	20,30	2R7
BWVS003225153R3□00	3.3	1MHz,1V	45	77	1.3(1.1)	1.6(1.4)	20,30	3R3
BWVS003225154R7□00	4.7	1MHz,1V	40	110	1.1(0.99)	1.4(1.2)	20,30	4R7
BWVS003225156R8□00	6.8	1MHz,1V	30	160	0.90(0.81)	1.1(0.99)	20,30	6R8
BWVS00322515100□00	10	1MHz,1V	25	220	0.78(0.70)	0.90(0.81)	20,30	100
BWVS00322515120□00	12	1MHz,1V	24	270	0.75(0.67)	0.85(0.76)	20,30	120
BWVS00322515150□00	15	1MHz,1V	21	320	0.60(0.54)	0.78(0.70)	20,30	150
BWVS00322515220□00	22	1MHz,1V	17	470	0.50(0.45)	0.67(0.60)	20,30	220
BWVS00322515330□00	33	1MHz,1V	12	700	0.40(0.36)	0.56(0.50)	20,30	330
BWVS00322515470□00	47	1MHz,1V	11	1000	0.34(0.30)	0.45(0.40)	20,30	470
BWVS00322515680□00	68	1MHz,1V	9.5	1400	0.29(0.26)	0.37(0.33)	20,30	680
BWVS00322515101□00	100	1MHz,1V	7.5	1900	0.23(0.20)	0.30(0.27)	20,30	101
BWVS00322515121□00	120	1MHz,1V	6.7	2800	0.20(0.18)	0.25(0.22)	20,30	121
BWVS00322515221□00	220	1MHz,1V	5.0	4700	0.15(0.13)	0.18(0.16)	20,30	221
BWVS00322515471□00	470	1MHz,1V	3.3	10000	0.10(0.09)	0.12(0.10)	20,30	471
BWVS00322515681□00	680	1MHz,1V	2.5	15000	0.08(0.07)	0.09(0.08)	20,30	681
BWVS00322515102□00	1000	100kHz,1V	2.0	23000	0.06(0.05)	0.07(0.06)	20,30	102


NOTE: □-tolerance M=±20% / T=±30%

1. Operating temperature range -55°C ~ 125°C (Including self - temperature rise)
2. Isat for Inductance drop 30% from its value without current.
3. Irms for a 40°C temperature rise from 25°C ambient.

BWVS00322515 Series Specification

8 BWVS00322515 Series

8.1 Construction:



8.2 Material List:

NO	Part	Material
1	Core	Ferrite
2	Terminal	Ag/Cu/Ni/Sn
3	Wire	Copper(180°C)
4	Epoxy	Magnetic powder resin

BWVS00322515 Series Specification

9 Reliability Of Wire Wound Power Inductors


1-1.Mechanical Performance

No	Item	Specification	Test Method
1-1-1	Vibration	Chip coil shall not be damaged after tested as test method	Oscillation Frequency:10Hz to 55 Hz to 10 Hz for 1 min Total Amplitude:1.5mm Testing Time:A period of 2 hours in each of 3 mutually perpendicular directions(Total 6 hours)
1-1-2	Solderability	The wetting area of the electrode shall be at least 95% covered with new solder coating	Solder:Sn/Ag3.0/Cu0.5 per-Heating:150°C±10°C/1min to 2min solder Temperature:245°C±5°C Immersion Time:4s±1s
1-1-3	Resistance to Soldering Heat	Appearance:No damage	Solder:Sn/Ag3.0/Cu0.5 per-Heating:150°C±10°C/1min to 2min solder Temperature:260°C±5°C Immersion Time:10s±1s

1-2.Environmental Performance

No	Item	Specification	Test Method														
1-2-1	Heat Resistance	Appearance: No damage Inductance Change:within±10%	Temperature:125℃±3℃ Time: 1000hrs Then measured after exposure in the room Condition for 24h±2h														
1-2-2	Cold Resistance		Temperature: -55℃±3℃ Time: 1000hrs Then measured after exposure in the room Condition for 24h±2h														
1-2-3	Humidity		Temperature: 40℃±2℃ Humidity:90%(RH) to 95%(RH) Time: 1000hrs Then measures after exposure in the room Condition for 24h±2h														
1-2-4	Temperature Cycle		One cycle: <table><tr><th>Step</th><th>Temperature (℃)</th><th>Time (min)</th></tr><tr><td>1</td><td>-55±3</td><td>30</td></tr><tr><td>2</td><td>25±2</td><td>3</td></tr><tr><td>3</td><td>125±3</td><td>30</td></tr><tr><td>4</td><td>25±2</td><td>3</td></tr></table> Total: 100cycles Measured after exposure in the room condition for 24hrs	Step	Temperature (℃)	Time (min)	1	-55±3	30	2	25±2	3	3	125±3	30	4	25±2
Step	Temperature (℃)	Time (min)															
1	-55±3	30															
2	25±2	3															
3	125±3	30															
4	25±2	3															

BWVS00322515 Series Specification



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	Above 217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	—	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	—
實際時間 Time result	—	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	—

NOTE :


1. Re-flow possible times : within 2 times
2. Nitrogen adopted is recommended while in re-flow
3. Products can only be soldered with reflow

BWVS00322515 Series Specification

10 Packaging:

10.1 Packaging -Cover tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



10.2 Packaging Quantity

TYPE	PCS/REEL
322515	2000

10.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
322515	178	60	9	1.5

BWVS00322515 Series Specification


10 Packaging:

10.4 Tape Dimensions in mm



TYPE	A0	B0	K0	D	E	W	P	P0	P2
322515	2.85	3.56	1.80	1.55	1.75	8	4	4	2

11 Recommended Land Pattern:



Dimensions in mm

TYPE	A	B	C
322515	2.6	1.2	1.0


12 Note:

- Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- Do not knock nor drop.
- All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- The storage period is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% RH or less).
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- The moisture sensitivity level (MSL) of products is classified as level 1.

BWVS00322515 Series Specification


12 Note:

7. Void Appearance tolerance Limit




Exposed wire tolerance limit of coating resin part on product side.
The unilateral should be no more than two holes.

$$\begin{aligned} A &\leq W/2 \text{ GOOD} \\ A &> W/2 \text{ NG} \end{aligned}$$



The appearance standard of the chipping size in top side.

$$\begin{aligned} B &\leq W/5 \text{ GOOD} \\ B &> W/5 \text{ NG} \end{aligned}$$











External appearance criterion for exposed wire









Exposed end of the winding wire at the side should be acceptable.

BWVS00322515 Series Specification









13 Graph: BWVS00322515 Series Graph











BWVS00322515 Series Specification











BWVS00322515 Series Specification



BWVS00322515 Series Specification



BWVS00322515 Series Specification



BWVS00322515 Series Specification

